

135-735 Thinline Framed Pivot Door & Panel Shower Enclosure

www.bascoshowerdoor.com

Product Features

Available in standard and custom configuration
Tempered safety glass
Pivot jambs to have a continuous vinyl seal
Top pivot pin to have safety washer to prevent accidental dislodging of the door

Metal Cuts

SC-505 header = Unit width
SC-505A curb = Unit width
SC-506 head and curb fill = Top and bottom rail + 3/8
SC-508 wall jamb = Unit ht. - 3/4
SC-511 180° post = Unit ht. - 3/4
SC-549 strike rail = Unit ht. - 3 1/8
SC-552 strike jamb = Unit ht. - 2
SC-582 pivot rail = Unit ht. - 3 1/8
SC-552 pivot jamb = Unit ht. - 2
SC-589 drip rail = SC-899 bottom rail - 11/16
SC-899 top and bottom rail = Glass width + 1 7/8

Options

Towel bar kits
Glass patterns
Finish

Calculations

Maximum allowable width of unit = 72
Maximum allowable height of unit = 84

Glass Size

Door glass width as determined
Door glass ht. = Unit ht. - 5
Panel glass width = Unit width - door glass width - 5
Panel glass ht. = Unit ht. - 1



135-735 Parts List

- A. 1 Curb (with weep slots)
- B. 2 Wall Jambs
- C. 6 Plastic Wall Anchors
- D. 6 #8 x 1 1/2 Truss Head Screws
- E. 2 Plastic Setting Blocks
- F. 1 Fixed Glass Panel
- G. 1 180° Post
- H. 1 Header
- J. 12 #8 x 1/4 Truss Head Screws
- K. 2 Clear Vinyl Jamb Seals
- L. 1 Glazed Door Panel
- M. 1 Pivot Jamb
- N. 1 Strike Jamb (Magnetic)
- P. 2 Snap-in Fillers
- R. 1 Drip Rail
- S. 2 Drip Plugs
- T. 1 Tapered Drip Vinyl
- V. 1 Roll of Double Stick Tape
- W. 2 #10 x 7/16 Sq. Head Set Screws
- X. 1 Nylon Spacer
- Y. 2 Nylon Pivot Bushings
- AA. 1 Security Washer
- BB. 1 Interior Door Handle
- CC. 1 Exterior Door Handle
- DD. 2 #6 x 1 1/4 Round Head Screws
- EE. 4 Pcs. Vert. Glazing Vinyl (72)
- FF. 2 Pcs. Horiz. Glazing Vinyl (48)

