

Revision B:

• MSZ-GE06/09/12/15/18NA-**8** and MSY-GE09/12/15/18NA-**8** have been added.

Please void OBH548 REVISED EDITION-A.

INDOOR UNIT PARTS CATALOG


No. OBB548
REVISED EDITION-B

Models

MSZ-GE06NA
MSZ-GE09NA
MSZ-GE12NA
MSZ-GE15NA
MSZ-GE18NA
MSZ-GE24NA
MSY-GE09NA
MSY-GE12NA
MSY-GE15NA
MSY-GE18NA
MSY-GE24NA

MSZ-GE06NA-8****
MSZ-GE09NA-8****
MSZ-GE12NA-8****
MSZ-GE15NA-8****
MSZ-GE18NA-8****

MSY-GE09NA-8****
MSY-GE12NA-8****
MSY-GE15NA-8****
MSY-GE18NA-8****



MSZ-GE06/09/12/15/18NA
MSY-GE09/12/15/18NA

CONTENTS

1. RoHS PARTS LIST..... 2
2. OPTIONAL PARTS..... BACK COVER

SERVICE MANUAL (OBH548)

NOTE:

RoHS compliant products have <G> mark on the spec name plate.

Mr.SLIM™

Revision A:

• MSZ-GE24NA and MSY-GE24NA have been added.

Revision B:


• MSZ-GE06/09/12/15/18NA-**[8]** and MSY-GE09/12/15/18NA-**[8]** have been added.

1


RoHS PARTS LIST

MSZ-GE06NA MSZ-GE09NA MSZ-GE12NA MSZ-GE15NA MSZ-GE18NA
MSY-GE09NA MSY-GE12NA MSY-GE15NA MSY-GE18NA

1-1. INDOOR UNIT STRUCTURAL PARTS



1-2. ACCESSORY AND REMOTE CONTROLLER



1-1. INDOOR UNIT STRUCTURAL PARTS


No.	RoHS	Part No.	Part name	Symbol in Wiring Diagram	Q'ty/unit								Remarks	
					MSZ-GE					MSY-GE				
					06 NA	09 NA	12 NA	15 NA	18 NA	09 NA	12 NA	15 NA		18 NA
1	G	E12 D68 234	BOX ASSEMBLY		1	1	1	1	1	1	1	1	1	
2	G	E12 E79 000	PANEL ASSEMBLY		1	1	1	1	1	1	1	1	1	Including No. 3,4,5
3	G	E12 408 142	CATCH		2	2	2	2	2	2	2	2	2	2 PC/SET
4	G	E12 913 067	SCREW CAP		2	2	2	2	2	2	2	2	2	2 PC/SET
5	G	E12 E79 010	FRONT PANEL		1	1	1	1	1	1	1	1	1	
6	G	E12 D68 100	CATECHIN AIR FILTER		2	2	2	2	2	2	2	2	2	1 PC/SET
7	G	E12 D68 975	CORNER BOX (RIGHT)		1	1	1	1	1	1	1	1	1	
8	G	E12 D68 970	INSTALLATION PLATE		1	1	1	1	1	1	1	1	1	

1-2. ACCESSORY AND REMOTE CONTROLLER

9	G	E12 E79 426	REMOTE CONTROLLER		1	1	1	1	1					KM09E
	G	E12 E83 426	REMOTE CONTROLLER							1	1	1	1	KM09F
10	G	E12 527 083	REMOTE CONTROLLER HOLDER		1	1	1	1	1	1	1	1	1	

**MSZ-GE06NA MSZ-GE09NA MSZ-GE12NA MSZ-GE15NA MSZ-GE18NA
MSY-GE09NA MSY-GE12NA MSY-GE15NA MSY-GE18NA**

1-3. INDOOR UNIT ELECTRICAL PARTS AND FUNCTIONAL PARTS



1-3. INDOOR UNIT ELECTRICAL PARTS AND FUNCTIONAL PARTS


No.	RoHS	Part No.	Part name	Symbol in Wiring Diagram	Q'ty/unit										Remarks
					MSZ-GE					MSY-GE					
					06 NA	09 NA	12 NA	15 NA	18 NA	09 NA	12 NA	15 NA	18 NA		
1	G	E12 751 509	BEARING MOUNT		1	1	1	1	1	1	1	1	1		
2	G	E12 001 504	SLEEVE BEARING		1	1	1	1	1	1	1	1	1		
3	G	E12 897 702	DRAIN HOSE		1	1	1	1	1	1	1	1	1		
4	G	E12 E79 235	NOZZLE ASSEMBLY		1	1	1	1	1	1	1	1	1		
5	G	E12 D68 040	VANE (UPPER)		1	1	1	1	1	1	1	1	1		
6	G	E12 D68 041	VANE (LOWER)		1	1	1	1	1	1	1	1	1		
7	G	E12 A89 303	VANE MOTOR	MV	1	1	1	1	1	1	1	1	1	UP & DOWN	
8	G	E12 D68 308	ROOM TEMPERATURE THERMISTOR	RT11	1	1	1	1	1	1	1	1	1		
9	G	E12 F14 452	ELECTRONIC CONTROL P.C. BOARD		1										
	G	E12 E79 452			1										
	G	E12 E80 452				1									
	G	E12 E81 452					1								
	G	E12 E82 452						1							
	G	E12 E83 452							1						
	G	E12 E84 452								1					
	G	E12 E85 452									1				
	G	E12 E86 452											1		
10	G	E12 E79 978	CONDUIT PLATE		1	1	1	1	1	1	1	1	1		
11	G	E12 E79 979	CONDUIT COVER		1	1	1	1	1	1	1	1	1		
12	G	E12 E79 440	POWER P.C. BOARD ※1		1	1	1	1	1	1	1	1	1		
13	G	E12 D68 307	INDOOR COIL THERMISTOR	RT12,RT13	1	1	1	1	1	1	1	1	1		
14	G	E12 B75 385	VARISTOR	NR11	1	1	1	1	1	1	1	1	1		
15	G	E12 A49 382	FUSE	F11	1	1	1	1	1	1	1	1	1	T3.15AL250V	
16	G	E12 E79 784	V.A. CLAMP		1	1	1	1	1	1	1	1	1		
17	G	E12 E79 300	INDOOR FAN MOTOR ※2	MF	1	1	1	1	1	1	1	1	1	RC0J40-□□	
18	G	E12 D68 333	MOTOR BAND		1	1	1	1	1	1	1	1	1		
19	G	E12 A89 302	LINE FLOW FAN		1	1	1	1	1	1	1	1	1		

※1 Including TERMINAL BLOCK with TERMINAL P.C. BOARD

※2 Including FAN MOTOR RUBBER MOUNT (2 PCS/SET)

MSZ-GE06NA MSZ-GE09NA MSZ-GE12NA MSZ-GE15NA MSZ-GE18NA
 MSY-GE09NA MSY-GE12NA MSY-GE15NA MSY-GE18NA


1-4. INDOOR UNIT HEAT EXCHANGER



No.	RoHS	Part No.	Part name	Symbol in Wiring Diagram	Q'ty/unit										Remarks	
					MSZ-GE					MSY-GE						
					06 NA	09 NA	12 NA	15 NA	18 NA	09 NA	12 NA	15 NA	18 NA			
1	G	E12 D68 620	INDOOR HEAT EXCHANGER		1	1	1				1	1				
	G	E12 D71 620							1	1			1	1		
2	G	E12 815 666	UNION (GAS) (ø9.52)		1	1	1				1	1				ø3/8
	G	E12 155 666	UNION (GAS) (ø12.7)					1	1				1	1		ø1/2
3	G	E12 151 667	UNION (LIQUID) (ø6.35)		1	1	1	1	1	1	1	1	1	1	1	ø1/4


MSZ-GE06NA-^[8] MSZ-GE09NA-^[8] MSZ-GE12NA-^[8] MSZ-GE15NA-^[8] MSZ-GE18NA-^[8]
 MSY-GE09NA-^[8] MSY-GE12NA-^[8] MSY-GE15NA-^[8] MSY-GE18NA-^[8]

1-5. INDOOR UNIT STRUCTURAL PARTS



No.	RoHS	Part No.	Part name	Symbol in Wiring Diagram	Q'ty/unit								Remarks	
					MSZ-GE					MSY-GE				
					06 NA -8	09 NA -8	12 NA -8	15 NA -8	18 NA -8	09 NA -8	12 NA -8	15 NA -8		18 NA -8
1	G	E12 D68 234	BOX ASSEMBLY		1	1	1	1	1	1	1	1	1	
2	G	E12 E79 000	PANEL ASSEMBLY		1	1	1	1	1	1	1	1	1	Including No. 3,4,5
3	G	E12 408 142	CATCH		2	2	2	2	2	2	2	2	2	
4	G	E12 913 067	SCREW CAP		2	2	2	2	2	2	2	2	2	2 PC/SET
5	G	E12 E79 010	FRONT PANEL		1	1	1	1	1	1	1	1	1	2 PC/SET
6	G	E12 F63 100	NANO PLATINUM FILTER		2	2	2	2	2	2	2	2	2	1 PC/SET
7	G	E12 D68 975	CORNER BOX (RIGHT)		1	1	1	1	1	1	1	1	1	
8	G	E12 D68 970	INSTALLATION PLATE		1	1	1	1	1	1	1	1	1	


1-6. ACCESSORY AND REMOTE CONTROLLER



9	G	E12 E79 426	REMOTE CONTROLLER		1	1	1	1	1						KM09E
	G	E12 E83 426	REMOTE CONTROLLER							1	1	1	1		KM09F
10	G	E12 527 083	REMOTE CONTROLLER HOLDER		1	1	1	1	1	1	1	1	1		

MSZ-GE06NA-⁸ MSZ-GE09NA-⁸ MSZ-GE12NA-⁸ MSZ-GE15NA-⁸ MSZ-GE18NA-⁸
MSY-GE09NA-⁸ MSY-GE12NA-⁸ MSY-GE15NA-⁸ MSY-GE18NA-⁸

1-7. INDOOR UNIT ELECTRICAL PARTS AND FUNCTIONAL PARTS



1-7. INDOOR UNIT ELECTRICAL PARTS AND FUNCTIONAL PARTS


No.	RoHS	Part No.	Part name	Symbol in Wiring Diagram	Q'ty/unit										Remarks
					MSZ-GE					MSY-GE					
					06 NA -8	09 NA -8	12 NA -8	15 NA -8	18 NA -8	09 NA -8	12 NA -8	15 NA -8	18 NA -8		
1	G	E12 751 509	BEARING MOUNT		1	1	1	1	1	1	1	1	1		
2	G	E12 001 504	SLEEVE BEARING		1	1	1	1	1	1	1	1	1		
3	G	E12 897 702	DRAIN HOSE		1	1	1	1	1	1	1	1	1		
4	G	E12 E79 235	NOZZLE ASSEMBLY		1	1	1	1	1	1	1	1	1		
5	G	E12 D68 040	VANE (UPPER)		1	1	1	1	1	1	1	1	1		
6	G	E12 D68 041	VANE (LOWER)		1	1	1	1	1	1	1	1	1		
7	G	E12 A89 303	VANE MOTOR	MV	1	1	1	1	1	1	1	1	1	UP & DOWN	
8	G	E12 D68 308	ROOM TEMPERATURE THERMISTOR	RT11	1	1	1	1	1	1	1	1	1		
9	G	E12 G41 452	ELECTRONIC CONTROL P.C. BOARD		1										
	G	E12 G42 452				1									
	G	E12 G43 452					1								
	G	E12 G44 452						1							
	G	E12 G45 452							1						
	G	E12 G46 452								1					
	G	E12 G47 452									1				
	G	E12 G48 452										1			
	G	E12 G49 452											1		
10	G	E12 E79 978	CONDUIT PLATE		1	1	1	1	1	1	1	1	1		
11	G	E12 E79 979	CONDUIT COVER		1	1	1	1	1	1	1	1	1		
12	G	E12 E79 440	POWER P.C. BOARD ※1		1	1	1	1	1	1	1	1	1		
13	G	E12 D68 307	INDOOR COIL THERMISTOR	RT12,RT13	1	1	1	1	1	1	1	1	1		
14	G	E12 B75 385	VARISTOR	NR11	1	1	1	1	1	1	1	1	1		
15	G	E12 A49 382	FUSE	F11	1	1	1	1	1	1	1	1	1	T3.15AL250V	
16	G	E12 E79 784	V.A. CLAMP		1	1	1	1	1	1	1	1	1		
17	G	E12 E79 300	INDOOR FAN MOTOR ※2	MF	1	1	1	1	1	1	1	1	1	RC0J40-□□	
18	G	E12 D68 333	MOTOR BAND		1	1	1	1	1	1	1	1	1		
19	G	E12 A89 302	LINE FLOW FAN		1	1	1	1	1	1	1	1	1		

※1 Including TERMINAL BLOCK with TERMINAL P.C. BOARD

※2 Including FAN MOTOR RUBBER MOUNT (2 PCS/SET)

MSZ-GE06NA-^[8] MSZ-GE09NA-^[8] MSZ-GE12NA-^[8] MSZ-GE15NA-^[8] MSZ-GE18NA-^[8]
 MSY-GE09NA-^[8] MSY-GE12NA-^[8] MSY-GE15NA-^[8] MSY-GE18NA-^[8]


1-8. INDOOR UNIT HEAT EXCHANGER



No.	RoHS	Part No.	Part name	Symbol in Wiring Diagram	Q'ty/unit								Remarks	
					MSZ-GE					MSY-GE				
					06 NA -8	09 NA -8	12 NA -8	15 NA -8	18 NA -8	09 NA -8	12 NA -8	15 NA -8		18 NA -8
1	G	E12 D68 620	INDOOR HEAT EXCHANGER		1	1	1			1	1			
	G	E12 D71 620						1	1			1	1	
2	G	E12 815 666	UNION (GAS) (ø9.52)		1	1	1			1	1			ø3/8
	G	E12 155 666	UNION (GAS) (ø12.7)					1	1			1	1	ø1/2
3	G	E12 151 667	UNION (LIQUID) (ø6.35)		1	1	1	1	1	1	1	1	1	ø1/4


MSZ-GE24NA
MSY-GE24NA

1-9. INDOOR UNIT STRUCTURAL PARTS



No.	RoHS	Part No.	Part name	Symbol in Wiring Diagram	Q'ty/unit		Remarks
					MSZ-GE24NA	MSY-GE24NA	
1	G	E12 F28 234	BOX ASSEMBLY		1	1	
2	G	E12 F76 000	PANEL ASSEMBLY		1	1	Including No. 3,4,5
3	G	E12 408 142	CATCH		4	4	4 PCS/SET
4	G	E12 F28 067	SCREW CAP		3	3	3 PCS/SET
5	G	E12 F28 010	FRONT PANEL		1	1	
6	G	E12 F28 100	NANO PLATINUM FILTER		2	2	1 PC/SET
7	G	E12 F28 975	CORNER BOX (RIGHT)		1	1	
8	G	E12 F28 976	CORNER BOX (LEFT)		1	1	
9	G	E12 F28 970	INSTALLATION PLATE		1	1	
10	G	-	AIR CLEANING FILTER (ELECTROSTATIC ANTI-ALLERGY ENZYME FILTER)		2	2	MAC-2310FT-E 2 PCS/SET


1-10. ACCESSORY AND REMOTE CONTROLLER



11	G	E12 C26 426	REMOTE CONTROLLER		1		KM07K
	G	E12 C29 426	REMOTE CONTROLLER			1	KM07M
12	G	E12 527 083	REMOTE CONTROLLER HOLDER		1	1	

MSZ-GE24NA
MSY-GE24NA

1-11. INDOOR UNIT ELECTRICAL PARTS AND FUNCTIONAL PARTS




No.	ROHS	Part No.	Part name	Symbol in Wiring Diagram	Q'ty/unit		Remarks
					MSZ-GE24NA	MSY-GE24NA	
1	G	E12 751 509	BEARING MOUNT		1	1	
2	G	E12 001 504	SLEEVE BEARING		1	1	
3	G	E12 408 702	DRAIN HOSE		1	1	
4	G	E12 F76 235	NOZZLE ASSEMBLY		1	1	
5	G	E12 F76 040	VANE (UPPER)		1	1	
6	G	E12 F76 041	VANE (LOWER)		1	1	
7	G	E12 C33 303	VANE MOTOR (HORIZONTAL)	MV1	1	1	UP & DOWN
8	G	E12 C32 303	VANE MOTOR (VERTICAL)	MV2	2	2	RIGHT & LEFT
9	G	E12 F28 541	WATER CUT		1	1	
10	G	E12 C32 308	ROOM TEMPERATURE THERMISTOR	RT11	1	1	
11	G	E12 F76 979	CONDUIT COVER		1	1	
12	G	E12 F76 978	CONDUIT PLATE		1	1	
13	G	E12 F28 468	POWER MONITOR RECEIVER SW P.C. BOARD		1	1	
14	G	E12 F28 095	POWER MONITOR RECEIVER HOLDER		1	1	
15	G	E12 F76 452	ELECTRONIC CONTROL P.C. BOARD ※ 1		1		
	G	E12 F77 452	ELECTRONIC CONTROL P.C. BOARD ※ 1			1	
16	G	E12 F28 307	INDOOR COIL THERMISTOR	RT12,RT13	1	1	
17	G	E12 B75 385	VARISTOR	NR11	1	1	
18	G	E12 A49 382	FUSE	F11	1	1	T3.15AL250V
19	G	E12 F76 784	V.A. CLAMP		1	1	
20	G	E12 F28 300	INDOOR FAN MOTOR ※2	MF	1	1	RC0J56-□□
21	G	E12 F28 333	MOTOR BAND		1	1	
22	G	E12 F28 302	LINE FLOW FAN		1	1	

※1 Including TERMINAL BLOCK with TERMINAL P.C. BOARD

※2 Including FAN MOTOR RUBBER MOUNT (2 PCS/SET)

MSZ-GE24NA
MSY-GE24NA
1-12. INDOOR UNIT HEAT EXCHANGER




No.	RoHS	Part No.	Part name	Symbol in Wiring Diagram	Q'ty/unit		Remarks
					MSZ-GE24NA	MSY-GE24NA	
1	G	E12 F29 620	INDOOR HEAT EXCHANGER		1	1	
2	G	E12 527 666	UNION (GAS)		1	1	ø5/8
3	G	E12 815 666	UNION (LIQUID)		1	1	ø3/8

2-1. AIR CLEANING FILTER (ANTI-ALLERGY ENZYME FILTER)

- AIR CLEANING FILTER removes fine dust of 0.01 micron from air by means of static electricity.
- Normal life of AIR CLEANING FILTER is 1 year. If AIR CLEANING FILTER is to be washed, soak AIR CLEANING FILTER in water (when showing dirt, in lukewarm water) and rinse it delicately, without removing the filter from the frame about once every 3 months.
- Clogged AIR CLEANING FILTER may reduce the air conditioner capacity or cause frost on the air outlet.
- Do not remove or attach AIR CLEANING FILTER during unit operation.

Model		Part No.
MSZ-GE06NA	MSZ-GE06NA - 8	MAC-408FT-E
MSZ-GE09NA	MSZ-GE09NA - 8	
MSZ-GE12NA	MSZ-GE12NA - 8	
MSZ-GE15NA	MSZ-GE15NA - 8	
MSZ-GE18NA	MSZ-GE18NA - 8	
MSY-GE09NA	MSY-GE09NA - 8	
MSY-GE12NA	MSY-GE12NA - 8	
MSY-GE15NA	MSY-GE15NA - 8	
MSY-GE18NA	MSY-GE18NA - 8	
MSY-GE18NA	MSY-GE18NA - 8	

Pull to remove from the air filter



Air cleaning filter
(Blue bellows type)



HEAD OFFICE: TOKYO BLDG., 2-7-3, MARUNOUCHI, CHIYODA-KU, TOKYO 100-8310, JAPAN