




# ADJUSTABLE STYLE 1 1/2" SINK TRAP WITH CLEANOUT PLUG, SCHEDULE 40 OUTLET PLUMBING PRODUCT SPECIFICATION



## INSTALLATION MEASUREMENTS

PART NO.	INLET OD	OUTLET OD SCHED 40	HEIGHT	LENGTH	Tube
	(A)	(B)	(C)	(D TO E)	GA
461XPCABS	1 1/4, 1 1/2	1 1/2	5	10 1/2	17
461XPCABS869	1 1/4, 1 1/2	1 1/2	5	10 1/2	17
461XPCPVC*	1 1/4, 1 1/2	1 1/2	5	10 1/2	17
461XPCPVC869	1 1/4, 1 1/2	1 1/2	5	10 1/2	17
461XSNPVC869	1 1/2	1 1/2	5	10 1/2	17

## PART # SUFFIX DESIGNATIONS

ABS - Schedule 40 ABS

PVC - Schedule 40 PVC

BN - Brass nuts

RB - Rough brass finish

CP - Chromium plated

X - Ground joint connection

PC - Polished finish

869 - Box Flange

\* Part #'s provided standard with Keeney's unique Red TPE "leak free technology" washers

## DESCRIPTION

Brass adjustable style 1 1/2" p-trap for plumbing fixture.

Constructed of 17 gauge seamless brass & cast brass elbow, Schedule 40 connector and chrome cover tube.

## INCLUDES:

- J-bend, elbow, slip nuts, and slip washers
- Chrome plated cover tube
- Heavy duty chromium finish
- Factory testing to ensure leak free performance

## INDUSTRY APPROVALS

- UPC/IAPMO
- CSA
- Mass Code
- LA Code

Listing of parts approved for specific codes available. See Keeney contact information below.

## SPECIFIER APPROVAL

Job Name	Date
Model	Qty
Wholesaler	
Contractor	
Architect	

**FOR MORE INFORMATION CALL 1-800-243-0526  
OR E-MAIL NCS@UPT.COM**

THE KEENEY MANUFACTURING COMPANY

[www.keeneymfg.com](http://www.keeneymfg.com)

*Keeney Representative  
Stamp or Label Here*