

SLOPE CEILING IC HOUSING

roject:	
ixture Type:	
ocation:	_
Contact/Phone:	_

STANDARD SLOPE: 2/12 to 6/12 PITCH (9° to 27°) INCANDESCENT LAMPS

IC926

PRODUCT DESCRIPTION

Slope ceiling IC Housing "Air-Loc*" • Energy efficient, sealed inner housing • Double wall housing construction • Can be completely covered with insulation • When used with Air-Loc Gasket (see accessories), stops infiltration and exfiltration of air, reducing heating and cooling costs.

PRODUCT SPECIFICATIONS

Lamp Lamp ratings based on trim selected – see reverse.

Socket Medium base porcelain with nickel-plated copper screw shell • Adjustable to position lamp perpendicular to floor.

Trims Trim selection shown on reverse.

Labels U.L. listed for through-branch wiring, damp locations and IP • Product thermally protected against improper use of lamps
 Union made • UL Listed/CSA certified • Trim No. 610 is wet location approved for covered ceiling applications.

Testing All reports are based on published industry procedures; field performance may differ from laboratory performance.

Product specifications subject to change without notice.

INSTALLATION


Real Nail 3 Bar Hangers Telescoping, patent-pending Real Nail 3 system permits quick placement of housing anywhere within 24" O.C. joists or suspended ceilings • Integral T-bar notch and clip secures housing in suspended ceiling grid – no accessory clips required • 24" expansion stop allows quick placement of fixture in standard grid spacing • Bars scored in two locations for fast, clean breaking, allowing housing installation in tight applications • Bars captive to mounting frame • Edge-mounted for extra strength • Captive bugle-headed ring shank nail for quick one-step installation and easy removal with claw hammer for fixture relocation • Quick-Loc slot and oversized locking set screw lock fixture in position • Bar hanger foot contoured to align to bottom of construction joist • Alternate mounting holes included.


Junction Box Pre-wired junction box provided with (5) ½" and (1) ¾" knockouts, (4) Non-metallic sheathed cable connectors and ground wire, U.L. listed/CSA certified for through-branch wiring, maximum 8 No. 12 AWG 90° C branch circuit conductors (4 in, 4 out) • Junction box provided with removable access plates • Knockouts equipped with pryout slots.

Mounting Frame 22-gauge die-formed galvanized steel mounting frame • Rough-in section (junction box, mounting frame, housing and bar hangers) fully assembled for ease of installation.

Housing IC housing, .032" aluminum sealed for Air-Loc Compliance • Access door for junction box accessibility • Inner housing is vertically adjustable to accommodate up to a 1" ceiling thickness • Designed to fit into 2 x 8 construction.

DIMENSIONS





ACCESSORIES

Catalog No.	Description	
ALG926	Air-Loc Gasket	

To order, specify catalog number.

PRODUCT CODES

Catalog Number	Input Voltage	Lamp Rating (max.)
IC926	120V	A19/MR16/BR30/R30/PAR30/PAR30L/PAR38



SLOPE CEILING IC HOUSING

STANDARD SLOPE: 2/12 to 6/12 PITCH (9° to 27°) **INCANDESCENT LAMPS**

IC926

TRIMS/LAMPS

	Cat. No.	Description	Max. Lamp Rating
	610B-WH ◆ 610W-WH ◆	Lensed Abalite Black Baffle Lensed Abalite White Baffle	50W PAR30
0	612C-WH 612G-WH 612B-WH 612HZ-WH 612HZ-SC 612W-WH 612WHZ-WH 612WHZ-ABZ	Multiplier Cone - Clear Alzak® Multiplier Cone - Gold Alzak® Multiplier Cone - Black Alzak® Multiplier Cone - Haze Multiplier Cone - Haze Multiplier Cone - White Multiplier Cone - Wheat Haze Multiplier Cone - Wheat Haze	75W PAR30, 90W PAR38, 65W BR30
	614B-WH 614B-SC 614B-ABZ 614B-BL 614W-WH	Downlight with Black Baffle Downlight with Black Baffle Downlight with Black Baffle Downlight with Black Baffle Downlight with White Baffle	90W PAR38
	616B-WH 616W-WH	Black Cylinder Spotlight with Black Baffle White Cylinder Spotlight with White Baffle	60W PAR16
	617W-WH	White Spotlight with White Baffle	35W MR16 supplied with magnetic transformer
	619B-WH 619W-WH	Eyeball in Black Baffle Eyeball in White Baffle	85W BR30

Trim Size: 75/k" O.D. (except Cat. Nos. 612 and 614 - 73/k" O.D.). Trim Finish: ABZ - Classic Aged Bronze, BL - Black, GP - Graphite, PW - Plastic White (Polycarbonate material shower trim), SC - Satin Chrome, SL - Silver, WH - White. Note: In Canada when insulation is present, Type IC fixtures must be used.

◆ UL Listed for use in wet location.

