



## Maxeen® Kitchen Sink SC3322DBG



### Features

- Durable high gloss finish.
- 8-3/8" (213 mm) basin depth.
- Offset bowl design.
- 33" (838 mm) x 22" (559 mm) x 8-3/8" (213 mm),

### Material

- Compression molded from our exclusive solid Vikrell® material.

### Installation

- Top-mount or undercounter installation.
- Four-hole point locators for 1-, 2- 3-, or 4-hole faucet installation.



For complete listing of available colors, go to [sterlingplumbing.com](http://sterlingplumbing.com).

### Codes/Standards


Greenguard UL 2818 - Gold

### STERLING® Warranty - Fixtures Made of Solid Vikrell Material

See website for detailed warranty information.

### Product Specification

Sink shall be 33" (838 mm) in length, 22" (559 mm) in width, and 8-3/8" (213 mm) in height. Sink shall be made of Vikrell® material. Sink shall be a offset double compartment and have four deck holes. Sink shall be top-mount or undercounter installation. Sink shall be STERLING Model SC3322DBG.



### Technical Information

All measurements are nominal.

Bowl configuration:	Offset
Installation:	Top-mount, Under-mount
Cutout:	Top-mount, 32-1/4" x 21-1/4" (819 mm x 540 mm) Top-mount, 13-1/4" x 16-1/16" (337 mm x 408 mm)
Bowl area (Left)	Length: 15-1/4" (387 mm) Width: 18-3/4" (476 mm) Bowl depth: 8-3/8" (213 mm)
Bowl area (Right)	Length: 13-1/4" (337 mm) Width: 16-1/16" (408 mm) Bowl depth: 8-3/8" (213 mm)
Number of deck holes:	4
Faucet hole(s):	1-7/16" (37 mm)
Drain hole:	3-1/2" (89 mm)

### Installation Notes

Install this product according to the installation guide.