

TECHNICAL SPECIFICATIONS

Gallery™ 5 Oval Whirlpool Bath

GAL6243 WLR 2XX Gallery 5 Oval Whirlpool Bath Left Hand (N845)
 GAL6243 WRL 2XX Gallery 5 Oval Whirlpool Bath Right Hand (N850)

Gallery™ 5 Oval Soaker Bath

GAL6243 BUX XXX Gallery 5 Oval Bath (N855)



INSTALLATION NOTES

Refer to installation instructions included with fixture before beginning installation. Please confirm product availability and specifications before commencing with any installation work.

PRODUCT SPECIFICATIONS AND AVAILABILITY ARE SUBJECT TO CHANGE WITHOUT NOTICE.

KEY DIMENSIONS

DIMENSIONS

62" L x 43" W x 19" H
 (1575 mm) L x (1092 mm) W x (543 mm) H

DRAIN/OVERFLOW

A: 14-3/4" (375 mm) B: 9-1/2" (241 mm)

CUTOUT

Template Provided P/N P186000

TOTAL WEIGHT

N845, N850: 798 lb (362 kg) / 43 lb/sq. ft. (210 kg/m²)

N855: 751 lb (341 kg) / 41 lb/sq. ft. (200 kg/m²)

OPERATING GALLONAGE

Min. 42 U.S. Gal. (197 Liters)

Max. 54 U.S. Gal. (204 Liters)

PRODUCT WEIGHT

N845, N850: 98 lb (44 kg)

N855: 51 lb (23 kg)

SKIRT MOUNTING

Not Available

ELECTRICAL SPECIFICATIONS - Models N845, N850 only

Requires a dedicated GFCI protected separate circuit.

Motor/Pump: 120 VAC, 15 AMP, 60 Hz.

RapidHeat™: 120 VAC, 15 AMP, 60 Hz.

HEATER (OPTIONAL) - Models N845, N850 only

Requires a dedicated GFCI protected separate circuit.



Product Shown: Gallery 5 Oval Whirlpool Bath Left Hand

Shown Model: N845


* Measurements inside unit represent cutout in floor to allow for drain/overflow.

FEATURES, UPGRADES & ACCESSORIES


- Left and Right Hand Drain Locations
- Accessories / Hardware:
 - Trip-Lever Drain Kit: #X559
 - Rotary Drain Kit, 26" Cable #8730
 - TheraPro™ Jet Rings #GU44
 - AccuPro™ Jet Rings #GU45
- Trim Kit Finishes Available:
 - (827) – Chrome
 - (826) – Brushed Nickel
 - (849) – Oil Rubbed Bronze



SIDE VIEW



END VIEW



DRAIN/OVERFLOW