


Z1088 BACKWATER VALVE GATE TYPE

SPECIFICATION SHEET	Γ
---------------------	---

TAG _____

Dimensional Data (inches and [mm]) are Subject to Manufacturing Tolerances and Change Without Notice



Dimensions In Inches					Approx.	
A Pipe Size	С	Е	M Wt. Lt			
4 [102]	8 [203]	12 [305]	15-3/4 [400]	80 [[36]	
6 [152]	10-1/2 [267]	14-1/2 [368]	19 [483]	120 [54]	

CONNECTIONS (Check/specify appropriate options)

ENGINEERING SPECIFICATION: ZURNZ1088

Gate Type Backwater Valve, Dura-Coated cast iron body with automatic PVC (4 [102] size only) flapper type backwater valve with O-ring adjacent to inlet and spade type bronze gate valve with O-ring seat insert adjacent to outlet easily controlled at floor level by covered handle engaging bronze non-rising stem. **Note:** Not designed nor intended to be used as a shut-off valve.

PIPE SIZE	(Specify size/type) CC	G-LENGTH	
4 [102]	HB X HB	Hub x Hub	14 [356]
6 [152]	HB X HB	Hub x Hub	16 [406]
4 [102]	HB X NH	Hub x No-Hub	18 [457]
6 [152]	HB X NH	Hub x No-Hub	20 [508]
4 [102]	NH X NH	No-Hub x No-Hub	18 [457]
6 [152]	NH X NH	No-Hub x No-Hub	16 [406]

PREFIXES

Z D.C.C.I. Body and Cover with PVC Flapper Valve, Bronze Check Valve, Gate, and Stem*

SUFFIXES

- ____ -BV Bronze Flapper Valve (4 [102] Size)
- -G Galvanized Cast Iron
- ____ -WH Wheel Handle
 - __ -12 12 [305] Extension
- ____ -24 24 [610] Extension

*REGULARLY FURNISHED UNLESS OTHERWISE SPECIFIED

REV. G DATE: 8/25/11 C.N. NO. 121989

DWG. NO. 58899 PRODUCT NO. Z1088