



Project: _____

Fixture Type: _____

Location: _____

Contact/Phone: _____

5" UNIVERSAL IC REMODEL HOUSING

INCANDESCENT LAMPS IC20R

PRODUCT DESCRIPTION

IC Air-Loc® Remodel Housing • Energy efficient, sealed housing
 • IC Remodel Housing for remodel application where back side of ceiling is not accessible • Installs through an opening in the ceiling from below • Secured in place by factory installed remodel springs • Can be completely covered with insulation • When used with Air-Loc Gasket (see accessories), stops infiltration and exfiltration of air, reducing heating and cooling costs • Trims shown with Air-Loc symbol **Air-Loc** do not require gasket.

PRODUCT SPECIFICATIONS

Lamp Lamp ratings based on trim selected—see reverse.

Socket Medium base porcelain with nickel-plated copper screw shell • Drop socket with spring to accommodate certain trim installation.



Trims Trim selection shown on reverse.

Labels U.L. listed for through-branch wiring, damp locations and IP • Product thermally protected against improper use of lamps
 • Union made • UL Listed/CSA certified • Trims 210, 211 and 212 are wet location approved for covered ceiling applications
 • Trims 215 and 216 are wet location approved for covered ceiling applications, **when used with outdoor rated lamps.**

Testing All reports are based on published industry procedures; field performance may differ from laboratory performance.

Product specifications subject to change without notice.

DIMENSIONS



5 1/2" CEILING CUTOUT

INSTALLATION

Junction Box Pre-wired junction box, UL listed/CSA certified for through-branch wiring maximum 4 No. 12 AWG 90° C branch circuit conductors (2 in, 2 out) • Junction box provided with removable access plate, (5) 1/2" knockouts, (4) Non-metallic sheathed cable connectors and ground wire • Knockouts equipped with pryout slots.

Housing IC housing, .032" aluminum sealed for Air-Loc Compliance • Remodel springs accommodate up to 1 1/8" ceiling thickness.

PRODUCT CODES

Catalog Number	Input Voltage	Lamp Rating (max.)
IC20R	120V	A19/BR30/PAR20/PAR30/PAR30L/R20/R30 (See reverse for max. trim rating)

ACCESSORIES

Catalog No.	Description
ALG5R	Air-Loc Gasket

To order, specify catalog number.

5" UNIVERSAL IC REMODEL HOUSING

INCANDESCENT LAMPS

IC2OR

TRIMS/LAMPS

	Cat. No.	Description	Max. Lamp Rating
	201-WH	Open Frame	65W BR30
**	205B-WH 205W-WH 205B-SC 205B-ABZ	BR30/PAR30 Black Baffle BR30/PAR30 White Baffle BR30/PAR30 Black Baffle BR30/PAR30 Black Baffle	50W PAR30
**	204C-WH 204G-WH 204B-WH 204PT-SC 204HZ-WH 204W-WH 204WHZ-WH 204WHZ-ABZ	BR30/PAR30 Cone - Clear Alzak® BR30/PAR30 Cone - Gold Alzak® BR30/PAR30 Cone - Black Alzak® BR30/PAR30 Cone - Pewter Alzak® BR30/PAR30 Cone - Haze BR30/PAR30 Cone - Gloss White BR30/PAR30 Cone - Wheat Haze BR30/PAR30 Cone - Wheat Haze	50W PAR30
**	206C-WH 206G-WH 206B-WH 206PT-SC 206HZ-WH 206WHZ-WH 206WHZ-ABZ	Deep Cone - Clear Alzak® Deep Cone - Gold Alzak® Deep Cone - Black Alzak® Deep Cone - Pewter Alzak® Deep Cone - Haze Deep Cone - Wheat Haze Deep Cone - Wheat Haze	50W PAR30
**	207C-WH 207G-WH 207B-WH 207W-WH 207HZ-WH 207WHZ-WH	Cone - Clear Alzak® Cone - Gold Alzak® Cone - Black Alzak® Cone - Gloss White Cone - Haze Cone - Wheat Haze	50W PAR20/R20
AIR-LOC	215B-WH ♦♦ 215W-WH ♦♦	BR30/PAR30 Black Baffle BR30/PAR30 White Baffle	65W BR30, 75W PAR30L, 75W PAR30 w/Socket Extender
AIR-LOC	216C-WH ♦♦ 216G-WH ♦♦ 216W-WH ♦♦ 216HZ-WH ♦♦ 216WHZ-WH ♦♦	Cone - Clear Alzak® Cone - Gold Alzak® Cone - Gloss White Cone - Haze Cone - Wheat Haze	65W BR30, 75W PAR30L, 75W PAR30 w/Socket Extender,
	208B-WH 208W-WH	Eyeball with Black Baffle Eyeball with White Baffle	50W PAR20/R20
	529-WH 529-SC 529-ABZ	PAR30 Eyeball PAR30 Eyeball PAR30 Eyeball	75W PAR30
	209-WH	Gimbal Ring with Flat Trim	75W PAR30
	688B-WH 688W-WH	Gimbal Ring with Black Baffle Gimbal Ring with White Baffle	50W PAR30
	689C-WH 689G-WH 689HZ-WH 689WHZ-WH 689WHZ-ABZ	Gimbal Ring in Clear Cone Gimbal Ring in Gold Cone Gimbal Ring in Haze Cone Gimbal Ring in Wheat Haze Cone Gimbal Ring in Wheat Haze Cone	50W PAR30
AIR-LOC	210-WH ♦ 210-SC ♦ 210-ABZ ♦	Lensed Shower/Closet Light Lensed Shower/Closet Light Lensed Shower/Closet Light	40W A19
AIR-LOC	211-PW ♦	Shower Trim	40W A19
AIR-LOC	212-WH ♦ 212-SC ♦ 212-ABZ ♦	Shower Trim Shower Trim Shower Trim	40W A15, 50W PAR30

Trim Size: 6 1/4" O.D. (except Cat No. 529 - 6 1/2" O.D.)
Trim Finish: ABZ - Classic Aged Bronze, BL - Black, GP - Graphite,
PW - Plastic White (Polycarbonate material shower trim),
SC - Satin Chrome, SL - Silver, WH - White.
Alzak is a registered trademark of Alcoa Corp.
Note: In Canada when insulation is present, Type IC fixtures must be used.

AIR-LOC JUNO IC housings meet IECC Energy Code requirements per ASTM E283.
Air-Loc® rated trims are pre-gasketed for minimum air leakage with IC housings.

♦ UL Listed for use in wet location.

♦♦ UL Listed for use in wet location with outdoor rated lamp.

** NOTE: TR5 Trim Ring compatible with 204, 205, 206, 207 trims.



1300 S. Wolf Road • Des Plaines, IL 60018 • Phone (847) 827-9880 • Fax (847) 827-2925
220 Chrysler Drive • Brampton, Ontario • Canada L6S 6B6 • Phone (905) 792-7335 • Fax (905) 792-0064
Visit us at www.junolightinggroup.com

Printed in U.S.A. ©2010 Juno Lighting, LLC.