



Adapters
U-Ground 3 Outlet

- 15 A rating
- 14/3 cord
- All u-ground connection
- 24” length



**PART
NUMBER**
8291

“Y” Adapter
Twist & Lock Male/Female

- 15 A rating
- 14/3 cord
- All U-ground connection
- 24” length



**PART
NUMBER**
8306

U-Ground to Twist & Tock

- Female twist and lock to male u-ground
- 15 A plug, 20 A connection
- 12/3 ST cord
- 12” length



**PART
NUMBER**
8299

Twist & Lock to U-Ground

- Male twist and lock to female u-ground
- 15 A plug, 20 A connection
- 12/3 ST cord
- 12” length



**PART
NUMBER**
8302

Twist & Lock to U-Ground

- 3 Outlet
- Female twist and lock to male u-ground
- 15 A plug, 20 A connection
- 12/3 ST cord
- 12” length



**PART
NUMBER**
8304

Thermostat Wire

- Solid copper conductors with PVC insulation, conductors twisted
- Color coded
- Bagged



PART NUMBER	LENGTH	WIRE TYPE
8320	25’	18/2
8321	50’	