

### **DW Series**



### **Dry Wall Access Doors**

**Doors** are ideally suited for new installations or for remodeling, in masonry, tile, wood or other wall and ceiling surfaces. Door features rounded safety corners.

**Door and Frame** are fabricated from 16 gage, galvannealed steel with a prime coat finish.

**Frame** is one piece construction, 1" wide and provides perfect concealment of the rough wall opening. Wall frame is provided with 1/4" mounting holes for fastening within the furred spaces allowing faster installation and fixing maximum clearance.

**Concealed Pivoting Rod Hinge** prevents distortion and closes door squarely. Doors 24" or larger are provided with a continuous piano hinge.

**Latch** is screwdriver operated.

**Finish** is a prime coat suitable for painting.

# **Guide Specification**

Provide Elmdor® DW Series, Dry Wall Access Doors (Specify model number and options.) Access door and frame shall be fabricated from 16 gage, galvannealed steel with a prime coat finish. The door shall have rounded safety corners and a concealed pivoting rod hinge. Frame shall be one piece construction with no mitres or welds on the face. Latch shall be screwdriver operated. Finish shall be a prime coat suitable for painting.

**DW** *Revised: 5/14/08* 



## MODEL NUMBER AND OPTIONS SELECTION

#### **BASE MODEL NUMBER**

DW Dry Wall Access Door (16 Gage Steel)

# **Suffix Options**

☐ - AKL Allen Key Latch

□ - CL Cylinder Lock (one per door)□ - MAS Masonry Anchor Straps

□ - SS Stainless Steel Construction.


(Type 304 No 4 Finish Satin Finish)


☐ - TH 'T' Handle

#### STANDARD AVAILABLE SIZES

Special sizes available upon request.

| NOMINAL<br>DOOR SIZE |                   |         |           |
|----------------------|-------------------|---------|-----------|
| (W X H)              | WALL OPENING      | LATCHES | WEIGHT    |
| DW 6" x 6"           | 6-1/2" x 6-1/2"   | 1       | 3 lbs.    |
| DW 8" x 8"           | 8-1/2" x 8-1/2"   | 1       | 3 lbs.    |
| DW 8" x 12"          | 8-1/2" x 12-1/2"  | 1       | 4 lbs.    |
| DW 10" x 10"         | 10-1/2" x 10-1/2" | 1       | 4 lbs.    |
| DW 12" x 12"         | 12-1/2" x 12-1/2" | 1       | 5.5 lbs.  |
| DW 12" x 16"         | 12-1/2" x 16-1/2" | 1       | 6 lbs.    |
| DW 12" x 18"         | 12-1/2" x 18-1/2" | 1       | 6.5 lbs.  |
| DW 12" x 24"         | 12-1/2" x 24-1/2" | 2       | 9.5 lbs.  |
| DW 14" x 14"         | 14-1/2" x 14-1/2" | 1       | 6 lbs.    |
| DW 14" x 20"         | 14-1/2" x 20-1/2" | 2       | 8 lbs.    |
| DW 14" x 24"         | 14-1/2" x 24-1/2" | 2       | 15 lbs.   |
| DW 15" x 15"         | 15-1/2" x 15-1/2" | 1       | 6.5 lbs.  |
| DW 16" x 16"         | 16-1/2" x 16-1/2" | 1       | 7.5 lbs.  |
| DW 16" x 20"         | 16-1/2" x 20-1/2" | 2       | 8.5 lbs.  |
| DW 16" x 24"         | 16-1/2" x 24-1/2" | 2       | 10 lbs.   |
| DW 18" x 18"         | 18-1/2" x 18-1/2" | 3       | 9 lbs.    |
| DW 18" x 24"         | 18-1/2" x 24-1/2" | 5       | 12 lbs.   |
| DW 18" x 36"         | 18-1/2" x 36-1/2" | 3       | 16 lbs.   |
| DW 20" x 20"         | 20-1/2" x 20-1/2" | 3       | 11 lbs.   |
| DW 20" x 24"         | 20-1/2" x 24-1/2" | 3       | 13 lbs.   |
| DW 20" x 30"         | 20-1/2" x 30-1/2" | 5       | 15 lbs.   |
| DW 22" x 22"         | 22-1/2" x 22-1/2" | 3       | 12 lbs.   |
| DW 22" x 30"         | 22-1/2" x 30-1/2" | 3       | 16 lbs.   |
| DW 24" x 24"         | 24-1/2" x 24-1/2" | 3       | 15 lbs.   |
| DW 24" x 30"         | 24-1/2" x 30-1/2" | 6       | 17 lbs.   |
| DW 24" x 36"         | 24-1/2" x 36-1/2" | 5       | 20.5 lbs. |
| DW 24" x 48"         | 24-1/2" x 48-1/2" | 7       | 28 lbs.   |
| DW 30" x 30"         | 30-1/2" x 30-1/2" | 7       | 21.5 lbs. |
| DW 32" x 32"         | 32-1/2" x 32-1/2" | 5       | 23 lbs.   |
| DW 36" x 36"         | 36-1/2" x 36-1/2" | 8       | 31.5 lbs. |
| DW 36" x 48"         | 36-1/2" x 48-1/2" | 6       | 35 lbs.   |
|                      |                   |         |           |





#### NOTES:

- 1. CONCEALED PIVOTING ROD HINGE
- 2. DOOR
- 3. FRAME
- 4. SCREWDRIVER OPERATED LATCH
- 5. MOUNTING HOLES

Dimensions are subject to manufacturer's tolerance of plus or minus 1/4". Elmdor/Stoneman assumes no responsibility for use of void or suspended data. Please visit **www.elmdorstoneman.com** for most current specifications. © Copyright 2008 Elmdor/Stoneman, City of Industry, CA, A Division of Acorn Engineering Company.

| SELECTION SUMMARY & APPROVAL FOR MANUFACTURING |          |  |  |
|------------------------------------------------|----------|--|--|
| Model Number & Options                         | Quantity |  |  |
| Company                                        | Date     |  |  |
| Contact                                        |          |  |  |
| Approval for Manufacturing/Signature           |          |  |  |

**DW** Revised: 5/14/08