

For Residential and Commercial Applications

Job Name		Engineer / Architect	
Job Location		Wholesaler	
Submittal Date		Contractor	

V1-**KC Speedi Plumb® Vinyl Faucet Connectors - Compression Inlet x KC Nosepiece Outlet

Use: For use in potable water distribution systems in accessible locations only

Design Features:

- **No kink hose.** The specially engineered reinforced PVC hose provides unique flexibility to prevent kinking and crimping
- **Greater strength and durability** with a tighter weave and two-layer bonded construction, outperforms conventional vinyl connectors
- **Longer wing nuts** ease installation for speedier connections
- **Rubber washers** provide a large pliable sealing surface and ensures a long lasting water tight connection
- **8-sided pneumatic crimp** provides greater dependability for reliable nut-to-hose connections


-  **No Lead**

Operating Specifications:

Temperature: 40° - 140° F, intermittent to 180° F

Pressure: 125 PSI maximum

Tubing Diameter: 0.300" I.D. (0.500" O.D.)



MATERIAL SPECIFICATIONS

Hose	<i>PVC with polyester braid reinforcement</i>
Barb	<i>Compliant brass</i>
Ferrule	<i>Zinc plated 1008 steel</i>
Nut	<i>C36000 brass, chrome plated</i>
Washer	<i>Rubber</i>
Compression Nut & Ring	<i>C36000 brass, (nut) chrome plated</i>

Part Listing:

- | | | |
|--------------------------|-----------|---|
| <input type="checkbox"/> | V1-12KC F | 3/8" compression x 3/8"compression x 12" length |
| <input type="checkbox"/> | V1-20KC F | 3/8" compression x 3/8"compression x 20" length |


This specification and all information contained herein is the confidential and exclusive property of BrassCraft Manufacturing, and shall not be disclosed to others without the written consent of BrassCraft. This specification must be returned to BrassCraft if requested.

400.117 V1-**KC SP Vinyl Faucet Connector - KC Nosepiece REV 01/11

BrassCraft®

© 2011 Brass-Craft Mfg.

V1-**KC Speedi Plumb® Vinyl Faucet Connectors - Compression Inlet x KC Nosepiece Outlet



PART DIMENSIONS (Inches)	
Model	DIM. A
V1-12KC	12.0 / 13.0
V1-20KC	20.0 / 21.0

Listings & Certifications:

- IAPMO listed to ASME A112.18.6-2003 (File # 0452)
- CSA listed to ASME A112.18.6-2003 / CSA B125 (File # 204593)
- CSA approved to California Health & Safety Code and Vermont Bill S.152 (Project # 2174785)



This specification and all information contained herein is the confidential and exclusive property of BrassCraft Manufacturing, and shall not be disclosed to others without the written consent of BrassCraft. This specification must be returned to BrassCraft if requested.

BrassCraft®