

### Supurr-Flex<sup>®</sup> pure aluminum, multi-layered flexible metallic duct



Fo420B, Fo425, Fo450

Model No.	Description
Fo420B	Supurr-Flex <sup>®</sup> multi-layered duct
Fo425	Supurr-Flex <sup>®</sup> multi-layered duct
Fo450	Supurr-Flex <sup>®</sup> multi-layered duct

#### Performance Data

for uninsulated aluminum, multi-layered flexible metallic duct

#### Maximum Velocity

- 4000 FPM

#### Maximum Rated Pressures

- all diameters 4" w.g. Pos.
- 4" dia., -4.0" w.g. Neg.

#### Operating Temperature Range


- 0°F to 265°F

**Pressure Drops** . . . . . (see chart)

#### General Information

- compressed Length . . . 25 ft. to 15" +/-
- this product was designed to replace vinyl duct and is easy to install
- fire retardant, NO exposed polyester inside or outside

#### Pressure Loss Diagram



Model No.	diameter	length
Fo420B	4" dia.	20 ft.
Fo425	4" dia.	25 ft.
Fo450	4" dia.	50 ft.