



Nylon Cable Ties PC 5970

Cable ties from L.H. Dottie – the perfect way to bundle, secure and identify. Consistent quality from statistically controlled molding processes insure the highest tensile strength with the lowest insertion force. Meets military specifications, AS-

33671, for dimensions, moisture content, tensile strength, life cycles, fluid immersion, melting point, and corrosion.

- Made In U.S.A.
- UL Recognized
- Manufactured With Filtered Nylon 6/6
- Finger Grips
- Angled Tail
- One Piece Design, Transition Rails, And 3 Tooth Pawl
- Rounded Edges

Standard Duty Cable Ties - Nylon PC 5970

CAT NO	UPC	COLOR	LENGTH	WIDTH	THICKNESS	TENSILE	BUNDLE DIA	STD BAG	WT/STD	BULK BAG	MSTR	UNIT
DT4	50004	Natural	4.12"	.095"	.042"	18 lb.	.875"	100	0.07#	1,000*	10,000	C
DT4B	50504	UV Black	4.12"	.095"	.042"	18 lb.	.875"	100	0.07#	1,000*	10,000	C
DT5	50005	Natural	5.84"	.140"	.049"	40 lb.	1.437"	100	0.14#	1,000*	10,000	C
DT5B	50505	UV Black	5.84"	.140"	.049"	40 lb.	1.437"	100	0.14#	1,000*	10,000	C
DT6	50006	Natural	7.56"	.180"	.052"	50 lb.	1.875"	100	0.29#	1,000*	10,000	C
DT6B	50506	UV Black	7.56"	.180"	.052"	50 lb.	1.875"	100	0.29#	1,000*	10,000	C
DT11	50011	Natural	11.25"	.180"	.052"	50 lb.	3.062"	100	0.38#	500*	5,000	C
DT11B	50511	UV Black	11.25"	.180"	.052"	50 lb.	3.062"	100	0.38#	500*	5,000	C
DT14	50014	Natural	14.56"	.180"	.052"	50 lb.	4.125"	100	0.48#	500*	5,000	C
DT14B	50514	UV Black	14.56"	.180"	.052"	50 lb.	4.125"	100	0.48#	500*	5,000	C

* Add "Bulk" to the end of part number for Bulk Bag.

Mil-Spec available upon request

Heavy Duty Cable Ties - Nylon PC 5970

CAT NO	UPC	COLOR	LENGTH	WIDTH	THICKNESS	TENSILE	BUNDLE DIA	STD BAG	WT/STD	MSTR	UNIT
DT14H	51014	Natural	15.09"	.300"	.076"	120 lb.	4.06"	50	0.52#	2,000	C
DT14HB	51514	UV Black	15.09"	.300"	.076"	120 lb.	4.06"	50	0.52#	2,000	C
DT21H	51021	Natural	25.25"	.340"	.090"	175 lb.	7.18"	50	0.87#	500	C
DT21HB	51521	UV Black	25.25"	.340"	.090"	175 lb.	7.18"	50	0.87#	500	C
DT36H	51034	Natural	37.25"	.340"	.090"	175 lb.	11.00"	50	1.54#	500	C
DT36HB	51534	UV Black	37.25"	.340"	.090"	175 lb.	11.00"	50	1.54#	500	C
DT48G	81705	Gray	48.50"	.340"	.090"	175 lb.	14.50"	50	1.65#	500	C

Mounting Hole Cable Ties - Nylon PC 5970

CAT NO	UPC	COLOR	LENGTH	SCREW HOLE	WIDTH	THK.	TENSILE	BUNDLE DIA	STD BAG	WT/STD	MSTR	UNIT
DTM6	52006	Natural	8.0"	No.10	.177"	.052"	50 lb.	1.75"	100	0.34#	5,000	C
DTM6B	52506	UV Black	8.0"	No.10	.177"	.052"	50 lb.	1.75"	100	0.34#	5,000	C
DTM14	52014	Natural	14.5"	No.10	.177"	.053"	50 lb.	4.00"	100	0.52#	5,000	C
DTM14B	52514	UV Black	14.5"	No.10	.177"	.053"	50 lb.	4.00"	100	0.52#	5,000	C



Mounting Bases - Nylon PC 5970

CAT NO	UPC	COLOR	SCREW HOLE	WTH. HOLE	HEIGHT	ADHESIVE	SLOT HEIGHT	SLOT WIDTH	STD BAG	WT/STD	MSTR	UNIT
DT75S	51075	Natural	No.4	.74"	.19"	Rubber	.05"	.20"	100	0.20#	1,000	C
DT75SB	51076	UV Black	No.4	.74"	.19"	Rubber	.05"	.20"	100	0.20#	1,000	C
DT100S	51100	Natural	No.6	.99"	.20"	Rubber	.06"	.20"	100	0.50#	1,000	C
DT100SB	51102	UV Black	No.6	.99"	.20"	Rubber	.06"	.20"	100	0.50#	1,000	C