

JOB NAME:

QUANTITY:

ITEM NO.:

PRODUCT NAME:

PRO SPRAY VALVE

☐ _____ SPECIAL CONFIGURATION
(CHECK BASE MODEL AND OPTIONS)



MODEL:

☐ 2990 W/ 2.65 GPM NOZZLE

OPTIONS OR MODIFICATIONS:

☐ SNAP-IN SCRUB BRUSH

☐ OTHER _____



FEATURES

- * FITS ALL BRANDS
- * SPRAY NOZZLE THREADED INTO BODY
- * HIGH STRENGTH BRONZE ALLOW HANDLE
- * BLACK DISH GUARD BUMPER
- * BUILT-IN SPRAY HANDLE CLIP
- * SHOWER SPRAY PATTERN

SYSTEM LIMITS

- * TEMP: 40°F MIN. TO 140°F MAX.
- * PRESSURE 200 PSI MAX. STATIC
- * 2.65 GPM AT 80 PSI

SHIPPING WEIGHT

- * 1.5 LBS

ANSI/A112.18.1M