

MISC & RELIEF VALVES

Fig. 1

Fig. 2


- Made from cross-linked polyethylene PEX tubing
- Rated for a 400°F waterway
- Can be cut to length with PEX tubing cutter
- PROSELECT dip tubes & discharge tubes are certified to applicable parts of the following standards:
 - UL 174 "Household Electric Storage Tank Water Heaters"
 - UL 1453 "Booster and Commercial Storage Tank Water Heaters"
 - ANSI Z21.10 "Storage Water Heaters"
 - IAS 1-89 "Non-metallic Dip Tubes"
 - ANSI/NSF 61 "Drinking Water System Components - Health Effects"
 - IAS/CSA 1-89, ANSI Z21.10.1 and Z21.10.3
 - ANSI Z21.98 "225°F temperature rating"
- UL & CSA certification files:
 - CSA Certificate of Compliance 1013314 (113104)
[Master Contract 150236] for "Dip Tubes - Nonmetallic"
 - UL MH25278 (cert to NSF 61)
 - UL MH17611 (cert to UL 174 and 1453)

DISCHARGE TUBE

| PROSELECT PN | OLD PROSELECT PN | DESCRIPTION | LENGTH | THREAD DIA. | PIC FOR FIGURE |
|--------------|------------------|--------------------|--------|-------------|----------------|
| PSW12507 | PF9002273PK | 3/4 T&P DCHRG PIPE | 60" | 3/4" | 1 |

DIP TUBES

| PROSELECT PN | OLD PROSELECT PN | DESCRIPTION | LENGTH | PIC FOR FIGURE |
|--------------|------------------|------------------------------|--------|----------------|
| PSW12501 | n/a | DIP TUBE UNIV | 52" | 2 |
| PSW12503 | n/a | DIP TUBE F/ 30/40/50 GAS HTR | 45" | 2 |

Warranty and Codes

These PROSELECT products carry a 1-year limited warranty except where noted.