



**Northland™**  
Top-mount Bar Sink  
**K-6579-3**

**Features**

- 15-inch minimum base cabinet width.
- KOHLER cast iron.
- Acid-resistant enamel finish.
- Single bowl.
- Three faucet holes.
- 15" (381 mm) x 15" (381 mm).

**Recommended Accessories**

K- 9000 P-Trap

**Optional Accessories**

K- 8801 Sink Strainer



ADA

**Codes/Standards**

ASME A112.19.1/CSA B45.2

ADA





ICC/ANSI A117.1


**KOHLER® Enameled Cast Iron Kitchen Sink - Lifetime Limited Warranty**

See website for detailed warranty information.

**Available Color/Finishes**

*Color tiles intended for reference only.*

Color	Code	Description
	0	White
	96	Biscuit
	47	Almond
	7	Black Black™



## Technical Information

All product dimensions are nominal.

Bowl configuration:	Single
Installation:	Top-mount
Cutout:	Top-mount, 14-1/4" x 14-1/4" (362 mm x 362 mm) with 1" (25 mm) radius corners
Bowl area	Length: 9-1/4" (235 mm) Width: 12" (305 mm) Bowl depth: 7" (178 mm)
Number of deck holes:	3
Faucet hole(s):	1-3/8" (35 mm)
Drain hole:	3-7/8" (98 mm)

## Notes

Install this product according to the installation guide.

ADA compliant when installed to the specific requirements of these regulations.