Rooftop Support Systems

MARS SERIES 939




Caddy® Pyramid ST Series Rooftop Support is roof-friendly, high-quality, versatile and durable for roofing applications.

Features:

- · Thermoplastic base is UV stabilized and weatherproof for long lasting
- Fixed-height mounting platform 4" off the roof surface and 10" of usable strut length, provides excellent load distribution
- Structurally engineered to support up to 1,000 lbs
- · Hot-dipped galvanized finish
- Superior corrosion protection
- · Supports the green building requirements, bases are made from recycled material and can contribute toward earning LEED credit

MARS NO.	Mfg No.	Height	Length (1)	Length (2)	Width	Surface Area	MAX. Rec. Load
93955	RPS360400	4"	10"	12.5"	8"	94.3"	1,000 lbs.

* Max. recommended load at 10.6 psi roof loading. Contact project or roofing engineer for maximum allowable load on individual project roof system.



A/C Disconnects

MARS SERIES 133

MARS AC Disconnect/GFCI Receptacle Combination

MARS AC Disconnect/ GFCI Receptacle Combination disconnects provide a convenient low cost means to satisfy NEC Article 210.63 requirements for HVAC/R Equipment Outlets and Article 406.8(B)(1) for Receptacle - Wet Locations. The NEMA 3R design insures a safe, weather tight installation for residential, light commercial and even some industrial applications.

Features & Benefits:

- 60 Amp, Non-Fused
- Pullout type
- 240 Volt AC, Single Phase
- 15 Amp, 125V GFCI Duplex Receptacle included

- Compact size 5"x7"x4"
- Removable cover
- Heavy galvanized 'G90' steel with highest quality electro-deposition finish resists corrosion and fading

UL & CUL Meets NEC		a raamig
MARS NO.	DESCRIPTION	MARS PACK
83308	Pullout disconnect/receptacle	4
83335	Generic Brand Disconnect Box	6
Midwest	Three Phase Pullout Disconnects - 240V -	NEMA 3R

Midwest three phase pull out disconnects and single phase non-automatic switches are manufactured of heavy zinc coated steel with highest quality electro-deposition paint finish for maximum corrosion resistance. The three phase disconnects are available with and without fuse protection. Fusible units require three fuses. NEMA 3R.

MARS NO.	DESCRIPTION	CASE QTY
83321	60 amp non-fused, three phase	4
83322	30 amp fused, three phase	4
83323	60 amp fused, three phase	4

Non-Automatic Disconnects - Nema 3R

Midwest Electric has developed a new NEMA 3R, non-automatic A/C disconnect with a patent pending on/off switch mechanism so there is no pullout to lose. This UL and CSA listed disconnect features: a keyhole mounting slot for easy installation, a removable door for easy wiring access, straight in and out lugs for quick connections and six 1/2" x 3/4" x 1" concentric knockouts.

The single phase non-automatic disconnects do not provide overcurrent protection with manual internal on/off switch.

MARS NO.	DESCRIPTION	CASE QTY
83328	60 amp, 240V, 10 HP	4





