
510 nVent CADDY EZ Riser - 5101000EG







- Slotted holes make assembly easy, eliminating loose hardware
- Serrated flange-head bolts eliminate need for wrenches on both bolt and nut
- Conforms with Federal Specification WW-H-171 (Type 8), Manufacturers Standardization Society (MSS) SP-58 (Type 8) ٠



Part Number	5101000EG
Material	Steel
Finish	Electrogalvanized
Pipe Size	10"
Outer Diameter (OD)	10 3/4"
Hole Size (HS)	11/16"
А	20 5/8"
В	2"
Static Load (F)	2,500 lb
Standard Packaging Quantity	70 рс
UPC	78285636948
EAN-13	8711893138603

Clamp is fitted for steel pipe and should be installed below a coupling or shear lug, with bolts torqued to recommended value. Slotted holes and bolts for pipe sizes up to 12" only.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.erico.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent 's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

© 2019 nVent All rights reserved nVent, nVent CADDY, nVent ERIFLEX and nVent LENTON are owned by nVent or its global affiliates.

All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without prior notice.

