Bronze Ball Valves

Two-Piece Body \bullet Full Port \bullet Bronze Trim \bullet 3⁄4" Hose Connection with Cap and Chain \bullet Blowout-Proof Stem

600 PSI/41.4 bar non-shock cold working pressure*


CONFORMS TO MSS SP-110

MATERIAL LIST									
	PART	SPECIFICATION							
1.	Handle Nut	Zinc Plated Steel							
2.	Handle	Zinc Plated Steel Clear Chromate Plastisol Coated							
3.	Threaded Pack Gland	Brass ASTM B 16 Alloy C36000							
4.	Packing	PTFE							
5.	Thrust Washer	Reinforced PTFE							
6.	Stem	Silicon Bronze ASTM B 371 Alloy C69300 or ASTM B 99 Alloy C65100							
7.	Ball	Brass ASTM B 124 Alloy C37700 or ASTM B16 Alloy C36000 EACH with Hard Chrome Plate							
8.	Seat Ring (2)	Reinforced PTFE							
9.	Body	Bronze ASTM B 584 Alloy C84400							
10.	Hose Body End	ASTM B 124 Alloy C37700							
11.	¹ Cap	Die Cast Brass							
12.	Gasket	Rubber							
13.	Chain	Brass							


¹ Cap is for hose end thread protection only. Not to be used for pressure containing purposes.



S-585-70-HC Solder x Hose



T-585-70-HC NPT x Hose



DIMENSIONS—WEIGHTS—QUANTITIES

		Dimensions																
	٦	T-585-70-HC		S-585-70-HC		IC		T-585-70-HC		S-585-70-HC								
Si	ze	e A		Α		E	В		<u> </u>		0	D		<u>T-585-70-HC</u>		<u>S-585-70-HC</u>		Master
In.	mm.	In.	mm.	In.	mm.	In.	mm.	In.	mm.	In.	mm.	In.	mm.	Lbs.	Kg.	Lbs.	Kg.	Ctn. Qty.
1⁄2	15	2.84	72	2.90	74	1.88	48	5.19	132	5.25	133	.50	13	.80	.36	.74	.34	100
3⁄4	20	3.31	84	3.47	88	2.25	57	6.25	159	6.25	159	.75	19	1.46	.66	1.42	.65	50

Note: solder end is designed to be soft-soldered into lines using solders with the melting point not exceeding 500°F. Higher temperature solders will damage the seat material. See installation sheet packaged with valves.

•For detailed operating pressure, refer to pressure temperature chart on page 42.



Visit our website for the most current information.

*Weighted average lead content $\leq 0.25\%$

NIBCO INC. WORLD HEADQUARTERS • 1516 MIDDLEBURY ST. • ELKHART, IN 46516-4740 • USA • PH: 1.800.234.0227 TECH SERVICES PH: 1.888.446.4226 • FAX: 1.888.336.4226 • INTERNATIONAL OFFICE PH: +1.574.295.3327 • FAX: +1.574.295.3455 www.nibco.com