

# Specifications



## **Two-Handle Bar Faucet**

Model: 8938

**NOTE**: THIS FAUCET IS DESIGNED TO BE INSTALLED THROUGH 2 HOLES, 1" MIN. DIA. AND 4" ON CENTER

## **DESCRIPTION**

- · Chrome plated metal construction
- 1/2" IPS connections
- Supplied with vandal resistant screws

## **OPERATION**

- Wrist Blade style handles with hot and cold color indicators
- Hot side counterclockwise (1/4) turn to open (clockwise to close))
- Cold side clockwise (1/4) turn to open (counter-clockwise to close)

#### FLOW

2.0 MAX. gpm (7.6 L/min) aerator

## **CARTRIDGE**


- 1224 cartridge design
- Nonmetallic and stainless steel construction

## **STANDARDS**

- Third party certified to meet ASME A112.18.1/CSA B-125.1, NSF61/9 and all applicable requirements referenced therein
- Contains no more than 0.25% weighted average lead content
- Complies with California Proposition 65 and with the Federal Safe Drinking Water Act
- ADA for lever handles

### **WARRANTY**

· Warranted for 5 years against material or manufacturing defects



## **CRITICAL DIMENSIONS**

(DO NOT SCALE)