

# LVC Showermaster®

## 55-5A

### ½" inlets & outlet


### CONCEALED PIPING

#### LVC Thermostatic Showermaster®

- Tub/shower installation
- Dura-trol® solid bimetal thermostat directly linked to valve porting to control the intake of hot and cold water and compensate for supply temperature or pressure fluctuations. Dura-trol® is highly responsive and cannot be damaged by extremes in temperature.
- Built-in shutoff for single handle operation
- Maximum operating pressure: 125 PSI (860 KPA)
- Adjustable high temperature limit stop set for 110°F\* (43°C)
- Dial, Off through Hot, with directional indicators
- ½" inlets and outlet
- 501P(G) Hand Shower (2.0GPM, 7.6 l/min), with glide rail, inline vacuum breaker, elbow and flange

Note: Leonard Valve Company reserves the right of product, or design modifications without notice or obligation.

Note: All piping and fittings not furnished by manufacturer.



<b>Engineer's Approval</b>	Job # _____
	Arch/Eng. _____
	Contractor _____