


# 100 Heavy Duty Loop Hanger – 1000300EG



- Recommended for the suspension of stationary non-insulated pipe lines
- Conforms with Federal Specification WW-H-171 (Type 10), Manufacturers Standardization Society (MSS) SP-58 (Type 10)



Part Number	1000300EG
Material	Steel
Finish	Pregalvanized
Pipe Size	3"
Outer Diameter (OD)	3 1/2"
Rod Size (RS)	1/2"
A	6 9/16"
B	3 3/16"
C	1 13/16"
Static Load (F)	1,000 lb
Certifications	cULus FM
Standard Packaging Quantity	50 pc
UPC	78285636062
EAN-13	8711893087703

FM is a registered certification mark of FM Approvals LLC, LTD. UL, UR, cUL, cUR, cULus and cURus are registered certification marks of UL LLC.

#### WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.erico.com](http://www.erico.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

© 2019 nVent All rights reserved

nVent, nVent CADDY, nVent ERICO, nVent ERIFLEX and nVent LENTON are owned by nVent or its global affiliates.

All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without prior notice.

