SPECIFICATION:						CLOSET CARRIER		
		714 SERIES COATED CAST IRON SIN				3	W/ RIGHT HAND VENT	
FITTING WITH 2" NO-HUB RIGHT-HAND OFFSET VENT, ADJUSTABLE CARRIER BODY, INVERTIBLE FOR SIPHON JET OR BLOWOUT CLOSETS,						VERTICAL W/ RIGHT HAND VENT		
		EXTENSION WITH INTEGRAL TEST (FOOT, PLATED HARDWARE AND NEC						
		,				SERIES	12714	
ANCHOR 5 1/8" FOR DIMENSION SHORTER THA								
		FOOT			I		MIN) CUT EXTENSION.	
				- 1 1				
		5" MAX			-2" NO-HUB VENT	(10-1/2 N	/AX) SPECIFY (-10)	
	1.67		F		A		IEND FEET BE SECURED	
	1.07			G) 5 3/8"		R WITH 1/2" BOLTS AND	
-		╶╅┼──╔╖║┵╞╧╫╧╢┷║╹		Ċ		ANCHUR	S (BY OTHERS).	
2	.94		B		_ Y _		HON JET ROUGHING	
	4						OR BLOWOUT NG OVER 12-1/2"	
	I	2 1/4"		5	5 1/2" ⊥		ON ORDER.	
FINISHED WALL - THE BOWL STABILIZER FOR BLOWOUT DIMS, USE:								
	FIX			A	DJUSTABLE FOOT ⊠	<u> </u>		
			٣ť					
			Ş		Т			
		7 1/2"						
			ل ا					
			٦					
18 1/4" MAX 12 5/8"								
		7 5/8"	1/	2"				
	L.				T T			
					Y			
	-XSD	EXTRA SPECIAL-DUTY 1,000 LB CARRIER	\square	-1		POSITIONI		
	-PF	PYLON FOOT, STD.		-6		· · · · · · · · · · · · · · · · · · ·		
	-OR -SD	O-RING CARRIER SPECIAL-DUTY 500 LB. CARRIER		-10 -24			ROUGH 10-1/2" WALL	
	-HS HUB & SPIGOT -H4 LEFT-HAND 4" NO-HUB BRANCH -HLH4 LEFT-HAND 4" HUB BRANCH			-24 -30	30 CAST IRON ADJ. EXTENSION W/ CONNECTOR			
				-30-2				
				-32				
	-RH4	RIGHT-HAND 4" NO-HUB BRANCH	\neg	-35	CARRIE	R FOR WHEEL	CHAIR HIGH ROUGH	
	-HRH4 RIGHT-HAND 4" HUB BRANCH			-49	,			
	-D4			-50			LET, OPPOSITE VENT	
	-HD4 -VP	DOUBLE 4" HUB BRANCHES VANDAL-PROOF TRIM		-53			/ INLET, UNDER VENT	
	••			-54	THREADE	D AUXILIARY I		
DATE OF LAST CHANGE: 12/02/2010 DIMENSIONS ARE SUBJECT TO MANUFACTURERS JOSAM COMPANY								
TOLERANCES AND CHANGE WITHOUT NOTICE.								
WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA. MICHIGAN CITY, INDIANA								