MULTI CONDUCTOR UNDERGROUND FEEDER CABLE





FEATURES

- Special stranding and packaging are available upon request.
- Direct Burial
- Sunlight Resistance
- Custom print available upon request.

APPLICATIONS

- Underground feeder and branch circuit cable.
- For use in accordance with Article 340 and other applicable parts of the National Electric Code.

CONSTRUCTION

Annealed bare copper insulated with high grade PVC. UL Listed for use in underground feeder and branch circuits. Temperature rating is 60°C to -25°C 600 Volts. Meets the requirements of UL 493.





SINGLE CONDUCTOR UNDERGROUND FEEDER CABLE



GAUGE	STRANDING	INSULATION THICKNESS		NOMINAL O.D.		STANDARD PACKAGE	SHIPPING WEIGHT ~LBS/
		in	mm	in	mm		1000 FT.
14	1/.0641	0.060	1.52	0.189	4.80	2500	27
12	1/.0808	0.060	1.52	0.206	5.23	2500	36
10	1/.1019	0.060	1.52	0.227	5.77	1000	50
8	1/.1285	0.080	2.03	0.297	7.54	1000	81
6	7/.0612	0.080	2.03	0.348	8.84	1000	123
4	7/.0772	0.080	2.03	0.398	10.11	500	180
2	7/.0974	0.080	2.03	0.454	11.53	500	255