


66 x 34 x 21 1/2 inches





## FEATURES ~

- Ergonomic bathing well
- Sculpted armrests
- Pre-leveled wood base
- Slip resistant floor
- Premium cast acrylic surface
- Limited 10-year warranty

#### **COLOR OPTIONS**

| Stock | Upgraded |
|-------|----------|
| White | Biscuit  |

## **AVAILABLE SYSTEM**

## WHIRLPOOL 💃

- Pneumatic on/off control
- 7 hydrotherapy jets
  - High-flow directional jets
  - Low-profile spinning micro-jets
- Whirlpool pump
- Safety suction system






<sup>\*</sup> Note: Availability of individual models varies by Regional Servicing Plant. Please consult your price list and/or A/B model list for availability in your area.









# ASCOT II

66 x 34 x 21 1/2 inches









FEATURES Dimensional Tolerance ± 3/8". Dimensions needed for site preparation should be measured from the unit. Aquatic assumes no responsibility for preparatory work.

| Type and Model #   | Material     | Jets | Pump   | Heater                     | Controls  | Drain     | Pkg. Wt.<br>Ibs |
|--------------------|--------------|------|--------|----------------------------|-----------|-----------|-----------------|
| Soaker #4466530    | Cast Acrylic | 0    | _      | _                          | -         | Universal | 116             |
| Whirlpool #4466531 | Cast Acrylic | 7    | 63 GPM | 1.5kW inline<br>(optional) | Pneumatic | Universal | 166             |

#### **DIMENSIONS** inches

| Width         | <b>Depth</b>  | Height         | Skirt  |
|---------------|---------------|----------------|--------|
| Overall / Net | Overall / Net | Overall / Net  | Height |
| 66            | 34            | 21 ½ /<br>19 ½ | -      |

#### SUMP DATA inches

| Capacity to<br>Overflow | Min. Operating Capacity | WIDTH @ | centerline | DEPTH @ | DEPTH @ centerline |  |
|-------------------------|-------------------------|---------|------------|---------|--------------------|--|
| gal                     | gal                     | Тор     | Bottom     | Тор     | Bottom             |  |
| 62                      | 47                      | 60 1/2  | 45         | 27 1/4  | 20                 |  |

### PLUMBING DIMENSIONS inches

| Α | В     | Drain<br>to Overflow | Drain<br>Diameter / Clearance |
|---|-------|----------------------|-------------------------------|
| 2 | 7 3/4 | 14                   | 2 / 1 1/4                     |

#### NOTES:

1) Where applicable, utilize cut-out templates packed with unit for deck cutouts.

#### ELECTRICAL DATA

| Component                            | Specification        | Requirement                                     |  |  |
|--------------------------------------|----------------------|---|--|--|
| Pump                                 | 5 AMP; 120 V         | 15 AMP; 120V, separate circuit;<br>Class A GFCI |  |  |
| Optional Heater<br>(whirlpool model) | 1.5KW; 12 AMP; 120 V | 15 AMP; 120V, separate circuit;<br>Class A GFCI |  |  |

<sup>2)</sup>  $16 \times 16$  minimum access required at pump/blower location(s).