



Linia™
Under-mount Bathroom Sink
K-2219

Features

- Vitreous china.
- Under-mount.
- Oval sculpted basin.
- Without overflow.
- No faucet holes; requires wall- or counter-mount faucet.
- 17" (432 mm) x 14" (356 mm)

Recommended Accessories

K- 9018 P-Trap

Components

Additional included component/s: Basin clamp accessory, and adjustable linkage.



Codes/Standards




ASME A112.19.2/CSA B45.1




KOHLER® One-Year Limited Warranty

See website for detailed warranty information.

Available Color/Finishes

Color tiles intended for reference only.

Color	Code	Description
	0	White
	96	Biscuit
	47	Almond



Technical Information

All product dimensions are nominal.

Bowl configuration: Single

Installation: Under-mount

Bowl area (Only) Length: 17" (432 mm)
Width: 14" (356 mm)
Water depth: 6-3/8" (162 mm)

Drain hole: 1-3/4" (44 mm)

Template: Under-mount, 1193643, required, not included

Notes

Install this product according to the installation guide.

NOTICE: Countertop manufacturer or cutter must use the current product template available at www.kohler.com, or by calling 1-800-4KOHLER. Kohler Co. is not responsible for cutout errors when the incorrect cutout template is used.