

DESCRIPTION

- · Brass construction
- 1/2" PEX connections
- Pressure balancing, four port, cycle valve

OPERATION

- Adjustable temperature limit stop to control maximum hot water temperature
- Pressure balancing mechanism maintain selected discharge temperature to ± 3°F

CARTRIDGE


- 1222 cartridge design
- Nonmetallic/nonferrous and stainless steel materials
- · Accommodates back to back installations

STANDARDS

 Third party certified to meet CSA B-125, ASSE 1016, CSA B-137.5, ASTM F1807, ASME A112.18.1M and all applicable requirements referenced therein

WARRANTY


- Lifetime limited warranty against leaks, drips and finish defects to the original consumer purchaser
- 5 year warranty if used in commercial installations



M•PACT POSI-TEMP® VALVE Pressure-Balancing Valve

Model: 62380 Bulk Packed (Bulk packed 12 per carton)

NOTE: See reverse side for illustrated parts



CRITICAL DIMENSIONS

(DO NOT SCALE)