

COLONY® SOFT SINGLE CONTROL LAVATORY FAUCET




2175.500 Shown

MODEL NUMBER:

- □ 2175.500 Colony Soft Single Control Centerset Metal lever handle. 50/50 Pop-up drain.
- □ 2175.506 Colony Soft Single Control Centerset

 Metal lever handle. Grid drain. Less pop-up rod and hole.
- □ 2175.505 Colony Soft Single Control Centerset Metal lever handle. Less drain. With pop-up hole, plug button and rod.
- □ 2175.504 Colony Soft Single Control Centerset

 Metal lever handle. Less drain. Less pop-up rod and hole.



GENERAL DESCRIPTION:

Single control lavatroy faucet on 4" centers. Washerless 40 mm ceramic disc valve cartridge with integral hot limit safety stop. Durable cast brass waterway with 1/2" male threaded brass inlet shanks. Metal body with color matched underbody. Metal lever handle with large "comfort zone". 1.2 gpm/4.5 L/min. maximum flow rate.

PRODUCT FEATURES:

Cast Brass Underbody with "City Shanks":

Strong and durable. Integral tabs on casting provide a wobble-free installation.

Ceramic Disc Valve Cartridge: Assures a lifetime of drip-free performance.

Adjustable Hot Limit Safety Stop: Limits the amount of hot water allowed to mix with cold. Reduces the risk of accidental scalding.

Lead Free: Faucet contains ≤ 0.25% total lead content by weighted average.

Longer Spout: Provides extended reach into lavatory.

Memory Position Valving: Allows user to turn valve on and off at preferred temperature setting without readjusting handle position each time.

Large "Comfort Zone": Allows easy fine tuning of temperature.

Simple Installation: Fast and easy one person installation. Faucet drops in from top. Quick spin nuts secure faucet in place.

SUGGESTED SPECIFICATION

Single control lavatory fitting shall feature cast brass waterways with 1/2" male inlet shanks. Shall also feature washerless 40 mm ceramic disc valve cartridge with integral hot limit safety stop. Fitting shall be American Standard Model # 2175.____.

© 2017 AS America, Inc.




COLONY® SOFT SINGLE CONTROL LAVATORY FAUCET

CODES AND STANDARDS

These products meet or exceed the following codes and standards:

ANSI A117.1 ASME A112.18.1 NSF 61/Section 9 and Annex G CSA B125.1



			Finish Options	
Product			Polished Chrome	PVD Brushed Nickel
Number	Description		002	295
2175.50	Colony Soft Single Control Centerset. 50/50 Pop-up drain.	(B)		
2175.506	Colony Soft Single Control Centerset. Grid drain. Less pop-up rod and hole.	(B)		N/A
2175.505	Colony Soft Single Control Centerset. Less drain. With pop-up rod and hole.	ÁDA		N/A
2175.504	Colony Soft Single Control Centerset. Less drain. Less pop-up rod and hole.	(A)		N/A

Meets the American Disabilities Act Guidelines and ANSI A117.1 Requirements for the physically challenged.

N/A = Not Available

AERATOR MODIFICATIONS***	Parts Suffix**
0.5 gpm (1.9 Lpm) Non-Aerated PCA* Spray	F05
0.5 gpm (1.9 Lpm) Non-Aerated Vandal Resistant PCA Spray	V05
1.0 gpm (3.8 Lpm) PCA Aerator	F10
1.0 gpm (3.8 Lpm) Vandal Resistant PCA Aerator	V10
1.2 gpm (4.5 Lpm) Vandal Resistant PCA Aerator	V12
1.5 gpm (5.7 Lpm) Vandal Resistant PCA Aerator	V15
1.5 gpm (5.7 Lpm) Non-Aerated Laminar PCA Flow Outlet	L15

^{*}PCA — Pressure Compensating

© 2017 AS America, Inc. Revised 5/17

^{**}To modify a product, add suffix after the 4th digit (ex. 2064F05101.002)

^{***}Modified product models are NOT WaterSense certified.