


# SMS500W

Wall or ceiling mount to control 500 watts incandescent or 100 watts Fluorescent lighting. Vandalproof lens. Full 180deg; view . Cover not included.

Color: White

Weight: 1.9 lbs



## Technical Specifications

### UL Listing:

Suitable for wet locations.

### Compatibility:

Compatible with most electronic ballasts. Not compatible with instant start ballasts.

### Voltage:

120 volts AC 60 Hz.

### Time Adjustment:

5 seconds to 15 minutes

### Quick Test Time:

5 second test time for fast installation. Works day or night.

### "No Hands" Auto Testing:

Auto mode starts after 4 minutes of testing. No adjustment needed.

### Photoelectric Control:

Deactivates lights during daylight. Fully adjustable for 24 hour operation or custom applications.

### Manual Override:

Double flip wall switch logic prevents activation by brief power outages. Resets after 8 hours. No extra wiring needed.

### Surge Protection:

Withstands up to 3000 volts

### LED Detection Indicator:

LED glows red day & night for "on guard" deterrence.

### RF Immunity:

Circuits fully shielded for maximum radio frequency immunity.

### Incandescent Watts Switched:

500 watts @ 120 volts

### Fluorescent Watts Switched:

250 watts @ 120 volts

### Ratings:

5 amps

### Power Consumption:

Negligible

### Time Delay:

5 seconds to 15 minutes

### Manual Switch:

None

### Ambient Light Sensing:

Adjustable

### Adjustments:

Time, ambient light & sensitivity

### Detection:

180deg; detection pattern

### Switching Capacity:

Relay On/Off Model Switches 240 watts when lights are mounted to sensor. 500 watts Incandescent or 240 watts Fluorescent of remotely mounted lighting @ 120 volts

### Patents:

RAB sensor and fixture designs are protected under U.S. and International Intellectual Property laws.

### Warranty:

5 year sensor warranty

