

### Features

- 36-inch minimum base cabinet width.
- Double-equal bowls.
- 8" Basin depth.
- Single faucet hole.
- SilentShield<sup>®</sup> sound-absorption technology offers quieter performance.
- Includes hardwood cutting board.
- Includes installation hardware.

### Material

• Premium 18-gauge stainless steel.

## Installation

• Top-mount.

### **Recommended Products/Accessories**

K-5117 Right-Bowl Sink Rack K-5119 Left-Bowl Sink Rack K-8801 Sink Strainer K-8799 Sink Strainer K-23726 Drain treatment K-23729 Stainless steel cleaner

## **Optional Products/Accessories**

K-3370 Cutting Board K-8813 Manual Sink Strainer with Tailpiece K-11352 Disposal Flange with Stopper



# Codes/Standards

ASME A112.19.3/CSA B45.4


#### Lifetime Limited Warranty for KOHLER<sup>®</sup> Stainless Steel Sinks See website for detailed warranty information.



Staccato<sup>™</sup> Top-mount Kitchen Sink K-3369-1



## Staccato<sup>™</sup> Top-mount Kitchen Sink K-3369-1



### **Technical Information**

All product dimensions are nominal.	
Bowl configuration:	Double equal
Installation:	Top-mount
Cutout:	Top-mount, 32-1/2" x 21-1/2" (826 mm x 546 mm) with 1" (25 mm) radius corners
Min. base cabinet width:	36" (914 mm)
Bowl area (Left):	Length: 17-1/16" (433 mm)
	Width: 13-15/16" (354 mm)
	Bowl depth: 8-5/16" (211 mm)
Bowl area (Right):	Water depth: 8" (203 mm) Length: 17-1/16" (433 mm)
Down area (Flight).	Width: 13-15/16" (354 mm)
	Bowl depth: 8-5/16" (211 mm)
	Water depth: 8" (203 mm)
Number of deck holes:	1
Faucet hole(s):	1-7/16" (37 mm)
Drain hole:	3-5/8" (92 mm)

### Notes

Install this product according to the installation instructions.

