

#### Features

- 33-inch minimum base cabinet width.
- KOHLER cast iron.
- Top-mount.
- Acid-resistant enamel finish.
- Double (large/medium) compartment.
- Three faucet holes with one accessory hole to the right.
- 33" (838 mm) x 22" (559 mm)

#### **Recommended Accessories**

K- 9000 P-Trap

#### **Optional Accessories**

- K- 6000 Sink Rack
- K- 6521 Sink Basket
- K- 8801 Sink Strainer



## Codes/Standards

ASME A112.19.1/CSA B45.2

### KOHLER<sup>®</sup> Enameled Cast Iron Kitchen Sink - Lifetime Limited Warranty

See website for detailed warranty information.

#### Available Color/Finishes

Color tiles intended for reference only.

Color	Code	Description
$\bigcirc$	0	White

)	96	Biscuit

#### 47 Almond

7 Black Black™



## Efficiency™ Top-mount Kitchen Sink K-5948-4

# Efficiency™ Top-mount Kitchen Sink K-5948-4

Notes

Install this product according to the installation guide.

## **Technical Information**

All product dimensions	s are nominal.
Bowl configuration:	Large/medium
Installation:	Top-mount
Cutout:	Top-mount, 31-7/8" x 1-1/2" (810 mm x
	38 mm) with 1" (25 mm) radius corners
Bowl area (Left)	Length: 16" (406 mm)
	Width: 19" (483 mm)
	Bowl depth: 6-3/4" (171 mm)
Bowl area (Right)	Length: 12" (305 mm)
	Width: 16" (406 mm)
	Bowl depth: 6-3/4" (171 mm)
Number of deck holes:	4
Faucet hole(s):	1-3/8" (35 mm)
Drain hole:	3-7/8" (98 mm)





