


### Features

- KOHLER cast iron
- Acid-resistant enamel finish
- Single compartment
- Top-mount countertop installation or optional wood stand installation
- Single-hole (-1) or (-1P)
- 2-hole (-2) or (-2P)
- 3-hole (-3) or (-3P)
- 25-1/2" (648 mm) x 24" (610 mm)

### TOP-MOUNT UTILITY SINK K-6608



### Codes/Standards Applicable

Specified model meets or exceeds the following:

- ASME A112.19.1/CSA B45.2

### Colors/Finishes

- 0: White
- Other: Refer to Price Book for additional colors/finishes

### Accessories

- CP: Polished Chrome
- NA: None applicable

### Specified Model

Model	Description	Colors/Finishes	
K-6608-1	Single-hole, on top of backsplash	<input type="checkbox"/> 0	<input type="checkbox"/> Other_____
K-6608-1P	Single-hole, on top of backsplash with painted underside of sink for wood sink stand installation	<input type="checkbox"/> 0	<input type="checkbox"/> Other_____
K-6608-2	2-hole, on front of backsplash (shown)	<input type="checkbox"/> 0	<input type="checkbox"/> Other_____
K-6608-2P	2-hole, on front of backsplash with painted underside of sink for wood sink stand installation	<input type="checkbox"/> 0	<input type="checkbox"/> Other_____
K-6608-3	3-hole, on top of backsplash	<input type="checkbox"/> 0	<input type="checkbox"/> Other_____
K-6608-3P	3-hole, on top of backsplash with painted underside of sink for wood sink stand installation	<input type="checkbox"/> 0	<input type="checkbox"/> Other_____
<b>Recommended Accessories</b>			
K-8801	Duostrainer® sink strainer	<input type="checkbox"/> CP	<input type="checkbox"/> Other_____

### Product Specification

The top-mount utility sink shall be made of cast iron with acid-resistant enamel finish. Sink shall be top-mount countertop installation or wood stand installation. Sink shall be single compartment. Sink shall have single-hole (-1) or (-1P), two-holes (-2) or (-2P), or three-holes (-3) or (-3P). Sink shall be 25-1/2" (648 mm) in length and 24" (610 mm) in width. Sink shall be Kohler Model K-6608-\_\_\_\_\_ -\_\_\_\_\_.

Optional Accessories		
K-6027	Wood grate	<input type="checkbox"/> NA
K-6034	Bottom bowl rack	<input type="checkbox"/> NA
K-6618	Wood sink stand	<input type="checkbox"/> NA



## Technical Information

Fixture*:	
Bowl area	20-9/16" (522 mm) x 17-1/8" (435 mm)
Water depth	11" (279 mm)
Water capacity	16.5 gal (62.4 L)
Faucet holes	1-3/8" (35 mm)
Drain hole	3-7/8" (98 mm)
* Approximate measurements for comparison only.	

## Installation Notes

Install this product according to the installation guide.

Countertop cut-out is 24-1/2" (622 mm) by 19-3/4" (502 mm) with 1/2" (13 mm) radius corners.



## Product Diagram