

A **KOHLER**, COMPANY

TRANQUII ITY®

Features

- Shipped with a bath liner to protect product during installation
- Compression molded from Sterling's exclusive solid Vikrell_® material
- · Lightly pebbled bottom surface for sure footing
- 10-year consumer/3-year commercial limited warranty
- · Available in either a high gloss or swirl gloss finish
- 60" (152.4 cm) x 43-1/2" (110.5 cm) x 18-1/8" (46 cm) rough-in dimensions include flanges
- 60" (152.4 cm) x 42" (106.7 cm) x 18-1/8" (46 cm) finished dimensions


Codes/Standards Applicable

Specified model meets or exceeds the following:

- ASTM E662
- ANSI Z124.1.2
- IAPMO/UPC
- HUD, UM Bulletin 73A
- NAHB Research Foundation, Inc.

42" (106.7 cm) OVAL BATH **61050100** ALSO 61051100, 71050100, 71051100





Colors/Finishes

- 0: White
- Other: Refer to Price Book for additional colors/finishes

Specified Model

Model	Description	Colors/Finishes	5
61050000	42" (106.7 cm) oval bath, with apron, 20 pack, swirl gloss finish	□ 0	☐ Other
61050100	42" (106.7 cm) oval bath, with apron, swirl gloss finish	□ 0	☐ Other
61051000	42" (106.7 cm) oval bath, without apron, 20 pack, swirl gloss finish	□ 0	☐ Other
61051100	42" (106.7 cm) oval bath, without apron, swirl gloss finish	□ 0	☐ Other
61051200	42" (106.7 cm) oval bath, without apron, 2 pack, swirl gloss finish	□ 0	☐ Other
61058000	Apron only, 20 pack, swirl gloss finish	□ 0	☐ Other
61058100	Apron only, swirl gloss finish	□ 0	☐ Other
71050000	42" (106.7 cm) oval bath, with apron, 20 pack, high gloss finish	□ 0	☐ Other
71050100	42" (106.7 cm) oval bath, with apron, swirl high finish	□ 0	☐ Other
71050200	42" (106.7 cm) oval bath, without apron, 20 pack, high gloss finish	□ 0	☐ Other
71051000	42" (106.7 cm) oval bath, without apron, high gloss finish	□ 0	☐ Other
71051100	42" (106.7 cm) oval bath, without apron, high gloss finish	□ 0	☐ Other
71051200	42" (106.7 cm) oval bath, without apron, 2 pack, high gloss finish	0	☐ Other
71058000	Apron only, 20 pack, high gloss finish	0	☐ Other
71058100	Apron only, high gloss finish	0	□ Other

TRANQUILITY®

Technical Information

	· · · · · · · · · · · · · · · · · · ·		
Fixture*:	basin area	top area	
Bathing well	42" (106.7 cm) x 23" (58.4 cm)	51" (129.5 cm) x 32-1/2" (82.6 cm)	
To overflow	water depth	capacity	
	11-1/4" (28.6 cm)	56 gal (212 L)	

^{*} Approximate measurements for comparison only.

Model	door maximum width		door maximum height		
All	*60" (152.4 cm)		*NA		
* Varies with alternative walls.					

Installation Notes

Install this product according to the installation guide.

Size the drain cutout to fit the drain assembly that will be used.

End stud positioning is critical if nailing-in flanges are to be used.

Double studding is recommended for pivot shower door installations.

Studs should be positioned roughly as shown for support clip or roofing nail installation.

When using the optional apron, use either the nailing-in flange on the apron or the three backing blocks to secure the apron.

