

CAPS

MOLDED  
FOR YOUR  
INDUSTRY

IntegriFuse<sup>TM</sup>



 **INTEGRITY**  
Fusion Products, Inc.

TOLL FREE 1-888-770-6330

[INTEGRITYFUSION.COM](http://INTEGRITYFUSION.COM)

# CAPS

## The difference MOLDED Makes

Molded Caps from Integrity Fusion Products offer performance, availability, and value that eliminate the need for fabricated fittings.

The molded difference includes:


- No inner fusion beads
- Fully Pressure Rated
- Wall thickness remains consistent throughout

IntegriFuse fittings are manufactured from 100% Virgin Resin with black high density bimodal polyethylene copolymer designed for use in, but not limited to, potable water, natural gas, industrial, landfill, oil & gas, and mining applications.

All IntegriFuse fittings meet ASTM-D2513 & ASTM-D3261 requirements.

All butt fusion, electrofusion, and transition fittings meet AWWA C-901/C-906, NSF-61, and NSF-372. IntegriFuse fittings are manufactured with resin having a material designation code of PE 3408, PE3608, PE 4710, and PE 100. FM Approved.

Integrity Fusion Products, Inc.  
270 Parkade Court  
Peachtree City, GA 30269  
Phone 770.632.7530 | Fax 770.632.7540  
www.IntegrityFusion.com  
Call Toll Free at 888.770.6330



## IPS

### SDR 17 (Standard Dimension Ratio) 125 PSI (Working Pressure at 73.4° F)

Nominal Size	A	B	C	D	Weight	Item Code
2" IPS	3.23"	0.140"	2.375"	2.52"	0.1 lbs.	100306
3" IPS	4.72"	0.206"	3.500"	3.70"	0.4 lbs.	100310
4" IPS	5.31"	0.264"	4.500"	3.98"	0.7 lbs.	100314
6" IPS	6.89"	0.390"	6.625"	4.84"	2.0 lbs.	100318
8" IPS	8.66"	0.507"	8.625"	5.83"	4.2 lbs.	100322
10" IPS	9.84"	0.633"	10.750"	6.30"	7.5 lbs.	100326
12" IPS	11.77"	0.750"	12.750"	7.52"	12.4 lbs.	100328

### SDR 11 (Standard Dimension Ratio) 200 PSI (Working Pressure at 73.4° F)

Nominal Size	A	B	C	D	Weight	Item Code	Notes
¾" IPS	2.55"	0.095"	1.050"	2.18"	0.1 lbs.	100300	-
1" IPS	2.64"	0.120"	1.315"	2.18"	0.1 lbs.	100302	-
1 ¼" IPS	2.77"	0.151"	1.660"	2.18"	0.1 lbs.	100303	-
1 ½" IPS	3.10"	0.173"	1.900"	2.42"	0.7 lbs.	100304	-
2" IPS	3.23"	0.216"	2.375"	2.52"	0.8 lbs.	100305	FM 200
3" IPS	4.72"	0.318"	3.500"	3.70"	0.9 lbs.	100309	FM 200
4" IPS	5.31"	0.409"	4.500"	3.98"	1.1 lbs.	100313	FM 200
6" IPS	6.89"	0.603"	6.625"	4.84"	2.9 lbs.	100317	FM 200
8" IPS	8.66"	0.785"	8.625"	5.83"	6.3 lbs.	100321	FM 200
10" IPS	9.84"	0.978"	10.750"	6.30"	10.9 lbs.	100325	FM 200
12" IPS	11.77"	1.160"	12.750"	7.52"	18.4 lbs.	100327	FM 200