

SUBMITTAL INFORMATION

Ductile Iron Wide Range Transition Coupling - (FC2W-xx style)



3" - 16" STYLE FC2W COUPLINGS FOR JOINING PIPES WITH VARIOUS O.D.'S



Nominal Pipe Size	RANGE (INCHES)	Range (mm)	Bolt Diameter	NUMBER OF BOLTS	Sleeve Length	Approx. Wt. Lbs	Part Number	✓ SUBMITTED ITEM(S)
3"	2.50 - 4.29	63.5 - 109.0	5/8"	3	7"	27	FC2W-3	
4"	3.96 - 5.60	100.6 - 142.2	5/8"	4	7"	35	FC2W-4	
6"	6.23 - 7.60	158.2 - 193.0	5/8"	4	7"	44	FC2W-6	
8"	8.40 - 9.75	213.3 - 247.6	5/8"	4	7"	52	FC2W-8	
10"	10.75 - 12.12	273.0 - 307.8	5/8"	6	9"	85	FC2W-10	
12"	12.75 - 14.38	323.8 - 365.2	5/8"	6	9"	97	FC2W-12	
16"	16.00 - 17.80	406.4 - 452.12	5/8"	8	10"	135	FC2W-16	

Pipes smaller than the published range may be joined using the FC2W coupling at a reduced pressure rating. Contact Ford Meter Box for details.

FEATURES

Center Sleeve:End Rings:Bolts and nuts:	Ductile iron per ASTM A536 Grade 65-45-12 Ductile iron per ASTM A536 Grade 65-45-12 High strength low alloy steel per ASTM A242 and AWWA C111 Bolts have an oval neck beneath the head which rests within the end ring to prevent bolts from rotating while tightening.
Coating:	Optional stainless steel bolts and nuts are available Black, fusion bonded epoxy applied per AWWA C213
Gasket:	Buna-N rubber per ASTM D2000, EPDM is available
Pressure Rating:	350 psi rated working water pressure in sizes 3" through 12" 250 psi rated working water pressure in 16"
 NSF 61 approved 	

Complies with AWWA C219

The Ford Meter Box Company considers the information in this submittal form to be correct at the time of publication. Item and option availability, including specifications, are subject to change without notice. Please verify that your product information is current.

FORD P.O. Box 443, Wabash, Indiana U.S.A. 46992-0443 Phone: 260-563-3171 / Fax: 800-826-3487 Overseas Fax: 260-563-0167 www.fordmeterbox.com 01/19/15	
---	--