KOHLER®

sok®

Overflowing Effervescence Bath

K-1189-RE

Features

- Left drain.
- Adjustable bath leveling system.
- Integral lumbar support.
- 75" (1905 mm) x 41" (1041 mm) x 25" (635 mm)

Material

- Acrylic

Hydrotherapy

- Effervescent bubbles with 11 ports.
- Built-in 4000 W heater.
- Cascading water over rim.
- Remote control.

Installation

- Drop-in

Required Accessories

K- 7193 Bath Drain

Recommended Accessories

K- 1601 Bath/Whirlpool Footstop



Codes/Standards

ASME A112.19.7/CSA B45.10
CSA B45.5/IAPMO Z124
ASTM E162
ASTM E662
UL 1795
CSA C22.2 No. 218.2
Greenguard UL 2818 - Gold
CARB P2

KOHLER® One-Year Limited Warranty

See website for detailed warranty information.

Available Color/Finishes

Color tiles intended for reference only.


Color	Code	Description
	0	White
	96	Biscuit


KOHLER®

sok®

Overflowing Effervescence Bath

K-1189-RE





Required Electrical Service

Two dedicated circuits required, protected with Class A Ground-Fault Circuit-Interrupter (GFCI) or Residual Current Device (RCD).

Pump:	240 V, 20 A, 50/60 Hz
Heater:	240 V, 20 A, 50/60 Hz

Technical Information

All product dimensions are nominal.

Installation:	Drop-in
Drain location:	Left
Basin area, bottom:	45" x 25-1/2" (1143 mm x 648 mm)
Basin area, top:	61-1/2" x 30-1/4" (1562 mm x 768 mm)
Weight:	275 lbs (124.7 kg)
Minimum floor load:	65 lbs/ft² (317.4 kg/m²)
Water depth:	23-1/2" (597 mm)
Water capacity:	142 gal (537.5 L)
Cutout:	Drop-in, 73-1/2" x 39-1/2" (1867 mm x 1003 mm)
Electrical component rating:	Pump: 240 V, 17 A, 50/60 Hz Heater: 240 V, 17 A, 50/60 Hz, 4000 W
Pump speed:	Variable

Notes

Measure your actual product for rough-in details.

Install this product according to the installation instructions.

The hot water supply should be 70% of the capacity of the bath or greater. Installations will vary.

Consult local and national codes for minimum air gap requirements when installing a spout on the faucet deck.

Unit must be filled through the bathing well.