


MC-10

HORIZONTAL, ADJUSTABLE, WATER CLOSET CARRIER


Specification: MIFAB® Series MC-10 (Specify -L for left or -R for right design) single, horizontal, adjustable, water closet carrier with lacquered cast iron fitting, 4" (102) no hub waste, 2" (51) no hub vent connection, lacquered cast iron gasketed adjustable faceplate, universal floor mounted cast iron foot supports, adjustable 8" tapered thread ABS nipple with integral test cap, neoprene bowl gasket, hardware, threaded rod protectors, polished chrome plated finishing cap nuts and rear anchor tie down support.

Function: Used with off the floor plumbing fixtures that are wall mounted and have no contact with the finished floor. The closet carrier is completely concealed within the wall and supports the load of the fixture through a faceplate and foot support system that is anchored to the floor. Sanitation underneath the fixture is more efficiently and economically maintained when installed off of the floor compared to floor mounted.


Note: 10 1/2" (267) minimum space required between front of foot and rear of anchor support. 8" (203) minimum in wall space required between back of rear anchor support and back of in wall foot supports. Note: Foot supports and faceplate are assembled at the factory before shipment in the typical siphon jet water closet configuration and are reversible for the blowout water closet design.




Note: 8" tapered thread ABS nipple shipped standard with MC-10 Series carriers. The universal faceplate assembly accepts all nipple variations, rolling thread (-OR), cast iron (-CI) and tapered thread ABS with adjustable horn (-AH).



Note: Rear anchor support is included with every





OPTIONAL VARIATIONS
8" ABS nipple with adjustable horn
12" ABS nipple with adjustable horn
Buy American Act compliant product
4" rolling thread cast iron nipple
6" rolling thread cast iron nipple
8" rolling thread cast iron nipple
12" rolling thread cast iron nipple
24" rolling thread cast iron nipple
Floor mount, back outlet fixture support
750 lb. rated heavy duty
1,000 lb. rated extra heavy duty
Hub and spigot connection
Left hand fitting
8" rolling thread ABS nipple

12" rolling thread ABS nipple
Pennsylvania Steel Act compliant product
Prefabricated carrier
Right hand fitting
Neoprene bowl gasket
Finishing / Tiling frame
Auxiliary support, recommended with nipple lengths over 12"
12" tapered thread ABS nipple
All galvanized
Vandal proof finish trim
Test plug for custom cast iron nipples
Nipple wrench
Flush valve support
Less fitting

left and right carrier

CALIFORNIA PROPOSITION 65 WARNING. This product contains chemicals known to the State of California to cause cancer and birth defects or other reproductive harm.

 Job Name:
 Page No:

 Section No:
 Contractor:

 Schedule No:
 Purchase Order No:

MIFAB reserves the right to make changes in material and design without formal notice and obligation.

USA: 1-800-465-2736 www.mifab.com CAN: 1-800-387-3880

Page CR1 2021-05-18