



# Memoirs®

## 6' Whirlpool Bath

### K-1418-AH



#### Features

- Center drain.
- Chromatherapy lighting allows you to select a preferred color scheme to suit your mood.
- Integral lumbar support.
- Textured bottom surface.
- Coordinates with other products in the Memoirs® collection.
- 72" (1829 mm) x 42" (1067 mm) x 22" (559 mm)

#### Material

- Acrylic

#### Hydrotherapy

- Eight fully adjustable Flexjet™ hydrotherapy jets for water flow and direction.
- Effervescent bubbles with eight ports.
- Built-in 1500 W heater.
- Lighted keypad control.
- Remote control.

#### Installation

- Drop-in

#### Recommended Accessories

- K- 1491 Bath/Whirlpool Pillow
- K- 1601 Bath/Whirlpool Footstop
- K- 7161-AF Bath Drain
- K- 24916 Wireless Music Kit



#### Codes/Standards






ASME A112.19.7/CSA B45.10  
CSA B45.5/IAPMO Z124  
ASTM E162  
ASTM E662  
UL 1795  
CSA C22.2 No. 218.2  
Greenguard UL 2818 - Gold  
CARB P2


#### KOHLER® One-Year Limited Warranty

See website for detailed warranty information.

#### Available Color/Finishes

*Color tiles intended for reference only.*

| Color  | Code | Description |
|--|------|-------------|
|  | 0    | White       |
|  | 96   | Biscuit     |
|  | 47   | Almond      |
|  | NY   | Dune        |
|  | G9   | Sandbar     |



## Required Electrical Service

One dedicated circuit required, protected with Class A Ground-Fault Circuit-Interrupter (GFCI) or Residual Current Device (RCD).

Pump, Heater: 240 V, 20 A, 50/60 Hz

## Technical Information

All product dimensions are nominal.

|                              |   |
|------------------------------|---|
| Installation:                | Drop-in   |
| Drain location:              | Center  |
| Basin area, bottom:          | 48" x 27" (1219 mm x 686 mm)  |
| Basin area, top:             | 60" x 30" (1524 mm x 762 mm)  |
| Weight:                      | 140 lbs (63.5 kg)   |
| Minimum floor load:          | 45 lbs/ft² (219.7 kg/m²)  |
| Water depth:                 | 16" (406 mm)  |
| Water capacity:              | 94 gal (355.8 L)  |
| Cutout:                      | Drop-in, 70-1/2" x 40-1/2" (1791 mm x 1029 mm)                        |
| Electrical component rating: | Pump: 240 V, 11 A, 50/60 Hz<br>Heater: 240 V, 6.3 A, 50/60 Hz, 1500 W |
| Pump speed:                  | Variable  |

## Notes

Measure your actual product for rough-in details.

Install this product according to the installation instructions.

The hot water supply should be 70% of the capacity of the bath or greater. Installations will vary.

If installing a rim-mount faucet, make sure there is no interference with drain overflow before drilling any holes. Consult local and national codes for minimum air gap requirements if installing a spout on the faucet deck.

This whirlpool is designed for drop-in installation only. It is not suited for use in a three wall alcove with an overhead shower.