



Job Name:

Job Type:

Comments:

Quantity:

8503-12: Single-Light New Castle Classic Wall Lantern Dimensions:



Width: 5 1/4"

Height wo/ Tail: 11"

Height: 14"

Extends: 5 3/4"

Wire: 6 1/2"

Mounting Proc.: Cap Nuts

Connection: Mounted To Box

Bulbs:

- 1 - medium A - Line 100w Max. 120v - Not included
- 1 - LED Medium LED A-19 8w 120v - Not included
- 1 - LED Medium LED A-19 13.5w 120v - Not included

Features:

- Clear bulb(s) recommended for this fixture

Material List:

1 Body - Aluminum - Black

Safety Listing:

UL Listed for Wet Locations
cUL Listed for Wet Locations

Instruction Sheets:

English (HC-223)
French (F-009)

Collection: New Castle

Classic Coach Style Single Light Lantern in Black Finish and Clear Beveled Glass Panels. Install With or Without Tail.

Classic outdoor wall lantern in black finish over solid brass and clear beveled glass. Installs with or without tail. (shown without tail height-10 3/4")

UPC #:785652850325

Finish: Black (12)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Panel	Glass	Clear Beveled	4									

Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Canopy			2 1/16	4 1/2	8 3/4	

Replacement Bulb Data:

Product #		Type	Base	Watts	Watts Consumed	Volts	Hours	Lumens	Temp (°K)	CRI
97308S		A-19	E-26 Medium			120v	50000	425	3000	85
97309S		A-19	E-26 Medium			120v	50000	850	3000	85

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	UPS Ship
Individual	8503-12	1	785652850325	6.25	7	9.78	0.248	2.7	Yes
Master Pack		3	10785652850322	20	7.58	10.5	0.921	9.1	Yes
NJ Pallet		240		48	40	72	80	648	No

NV Pallet		240		48	40	72	80	648	No
-----------	--	-----	--	----	----	----	----	-----	----