

MAXWELL® Round Front Toilet

12" Rough-in



Features:

- Low Consumption 1.6 gpf (6.0 Lpf)
- Round Front Bowl
- Slim Line Tank
- Glazed Trapway
- Reverse Trap
- Front Jet Flushing Action
- Front Tank Lever
- White, Bone, Biscuit
- 2 Bolt Caps
- Optional insulated tank to minimize condensation (use tank #28-492)


Dimensions:

Height 28 1/4"
Width18 1/2"
Depth26 3/4"
Rough-in12"
Water Surface from Rim $5 \ ^{3}/_{4}"$
Trapway (min)2"
Water Surface9 1/2" x 8"
Water Seal 2 ³ / ₄ "
Shipping Weight88 lbs



Specifications: *Bowl*—#21-752 Round Front Seat not included

Tank-#28-490



THIS FIXTURE QUALIFIES
ACCORDING TO ASME TEST
PROCEDURES AS A LOW
CONSUMPTION WATER CLOSET
WITH AN AVERAGE CONSUMPTION
OF 1.6 GAL. OR LESS.






www.gerberonline.com

Job Name	
Date	
Model Specified	
Quantity	
Customer	
Contractor	
Architect/engineer	

21-402 Round Front, 12" Rough-in (Bowl 21-752 with Tank 28-490)



NOTES:

All dimensions are in inches.

Illustrations may not be drawn to scale.

IMPORTANT:

Dimensions of fixtures are nominal and may vary within the range of tolerances established by ASME Standard A 112.19.2.

THIS FIXTURE QUALIFIES ACCORDING TO ASME TEST PROCEDURES AS A LOW CONSUMPTION WATER CLOSET WITH AN AVERAGE CONSUMPTION OF 1.6 gpf (6 Lpf) OR LESS.

VITREOUS CHINA TOILET