



Job Name:

Job Type:

Comments:

Quantity:

61060-962: Single-Light Sussex Mini-Pendant



Dimensions:

Diameter: 7 1/2"

Height w/ Chain: 58 1/2"

Height: 7 1/2"

Wire: 120" (color/Clear)

Chain: 12"

Mounting Proc.: Cap Nuts

Connection: Mounted To Box

Bulbs:

- 1 - medium A - Line 100w Max. 120v - Not included
- 1 - LED Medium LED A-19 8w 120v - Not included
- 1 - LED Medium LED A-19 13.5w 120v - Not included

Features:

- A decorative canopy is included

Material List:

- 1 Body - Steel - Brushed Nickel
- 1 Chain - Steel - Brushed Nickel

Safety Listing:

- UL Listed for Dry Locations
- cUL Listed for Dry Locations

Instruction Sheets:

- English (HC-387)
- French (F-004)

Collection: Sussex

Sussex One Light Mini Pendant in Brushed Nickel Finish with Satin White Glass Shade. Three 12 Inch Stems, Chain and Canopy Included

Yesterday's styling... today's finish - Brushed nickel finish over solid brass, with satin white glass. Includes three interconnecting 12" stems, 12" of chain, and canopy.

For Additional Stems, Order 9199-962; Design #: D20066

UPC #: 785652610615

Finish: Brushed Nickel (962)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Shade	Glass	Satin White	1				4 1/8	7 1/2	1 11/16			

Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Canopy	3			6 5/8		

Replacement Bulb Data:

Product #	Type	Base	Watts	Watts Consumed	Volts	Hours	Lumens	Temp (°K)	CRI
97308S	A-19	E-26 Medium			120v	50000	425	3000	85
97309S	A-19	E-26 Medium			120v	50000	850	3000	85

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	UPS Ship
Individual	61060-962	1	785652610615	15.75	9.5	7	0.606	4.4	Yes

NJ Pallet		165		48	40	74.25	82.5	726	No
NV Pallet		108		48	40	71.25	79.167	472.2	No