



Job Name:

Job Type:

Comments:

Quantity:

31050-962: Three-Light Canterbury Chandelier



Dimensions:

Diameter: 24"

Height w/ Chain: 137"

Height: 15"

Wire: 144" (color/Clear)

Chain: 120"

Mounting Proc.: Center Lock-Up

Connection: Mounted To Box

Bulbs:

- 3 - medium A - Line 100w Max. 120v - Not included
- 3 - LED Medium LED A-19 8w 120v - Not included
- 3 - LED Medium LED A-19 13.5w 120v - Not included

Features:

- Supplied with 12' of Wire Pre-laced through 10' of Chain

Material List:

- 1 Arms - Steel - Brushed Nickel
- 1 Chain - Steel - Brushed Nickel

Safety Listing:

- UL Listed for Dry Locations
- cUL Listed for Dry Locations

Instruction Sheets:

- English (HC-652)
- French (F-004)

Collection: Canterbury

Three Light Chandelier in Brushed Nickel Finish with Satin Etched Glass Shades.

Three Light Canterbury Chandelier with Brushed nickel Finish and Satin Etched Glass.

Design #: D10028; Family name: Canterbury

UPC #:785652310591

Finish: Brushed Nickel (962)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Shade	Glass	Satin Etched	1					6 15/16				

Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Canopy			1	5		

Replacement Bulb Data:

Product #	Type	Base	Watts	Watts Consumed	Volts	Hours	Lumens	Temp (°K)	CRI
97308S	A-19	E-26 Medium			120v	50000	425	3000	85
97309S	A-19	E-26 Medium			120v	50000	850	3000	85

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	UPS Ship
Individual	31050-962	1	785652310591	19.75	7.75	18.5	1.639	10.8	Yes
NJ Pallet		48		48	40	77	85.556	518.4	No

NV Pallet		40		48	40	72	80	470	No
-----------	--	----	--	----	----	----	----	-----	----