



# **Technical Product Specifications**

Supurr-Vent® Louvered Vent Hood without grid -5", 6" & 7" diameter



HS5W, HS5B, HS6W, HS6B



| Model No.         | Description | Color |
|-------------------|-------------|-------|
| HS <sub>5</sub> W | Hood        | White |
| HS <sub>5</sub> B | Hood        | Brown |
| HS6W              | Hood        | White |
| HS6B              | Hood        | Brown |
| HS7W              | Hood        | White |

## Performance Data

for all plastic molded louvered vent hoods

- Calcium filled Polypropylene
- Melting point: 325° F+
- UV Inhibitor added

#### **Technical Data**

#### Free Air

5" dia. = 22.5 square inches


6" dia. = 27 square inches


7" dia. = 31.5 square inches


## **General Information**


- 5", 6" & 7" diameter opening
- · quick, easy installation
- is very attractive and comes in a variety of sizes and two colors
- opens with ease for maximun airflow
- durable weather resistant
- curved louvers for quieter operation

| Model No.         | Α                   | В                  | C  |
|-------------------|---------------------|--------------------|----|
| HS <sub>5</sub> W | 77/8"               | 7 <sup>1</sup> /2" | 5" |
| HS <sub>5</sub> B | 77/8"               | 7 <sup>1</sup> /2" | 5" |
| HS6W              | 77/8"               | 7 <sup>1</sup> /2" | 6" |
| HS6B              | 77/8"               | 7 <sup>1</sup> /2" | 6" |
| HS7W              | 9 <sup>1</sup> /16" | 81/2"              | 7" |









**Rear View** 

6/01 **DEFLECTO CORPORATION** • P.O. Box 50057 • Indianapolis, IN 46250 • www.deflecto.com DEFLECTO/Canada Ltd. • St. Catharines, Ontario • Canada L2M 3Y2