GATE 148

BRONZE

125 lb. SWP-200 lb. WOG† • General Service
Solid Wedge Disc • Rising Stem
Threaded Bonnet • Gland Packed • Threaded Ends

4" size has split wedge and bolted bonnet. It is not covered in MSS SP-80.

SPECIFICATIONS

148 Conforms to: MSS SP-80. Type 2, Class 125, Threaded Ends.


MATERIAL LIST

PART	MATERIAL	ATERIAL SPECIFICATION	
Body	Bronze	ASTM B 62	
Bonnet	Bronze	ASTM B 62	
Wedge	Bronze	ASTM B 62	
Stem	Bronze	ASTM B 62	
Stuff Nut	Brass	ASTM B283 C37700	
Gland	Brass	ASTM B124 C37700	
Wheel Nut	Brass	Commercial	
Handwheel	Mall. Iron	Commercial	
Packing	Graphite	Commercial	
Name Plate	Sh. Alum.	Commercial	
	Body Bonnet Wedge Stem Stuff Nut Gland Wheel Nut Handwheel Packing	Body Bronze Bonnet Bronze Wedge Bronze Stem Bronze Stuff Nut Brass Gland Brass Wheel Nut Brass Handwheel Mall. Iron Packing Graphite	

Not used on 1/2" and smaller.

DIMENSIONS - INCHES / MILIMETERS					
Units	Size	Α	В	С	C _v
Inches	1/4	1.75	4.38	2.00	5.6
mm	6.4	44.5	111.1	5.8	
Inches	3/8	1.81	4.38	2.00	10.7
mm	9.5	46.1	111.1	5.8	
Inches	1/2	2.00	4.38	2.00	17.6
mm	12.7	50.8	111.1	5.8	
Inches	3/4	2.13	5.84	2.50	32.0
mm	19.1	54.0	148.4	63.5	
Inches	1	2.56	7.06	2.75	54.0
mm	25.4	65.1	179.4	69.9	
Inches	1 1/4	2.78	8.78	3.13	97.0
mm	31.8	70.6	223.0	79.4	
Inches	1 1/2	2.81	9.50	3.50	135.0
mm	38.1	71.5	241.3	88.9	
Inches	2	3.31	11.50	3.75	230.0
mm	50.8	84.2	292.1	95.3	
Inches	2 1/2	4.19	14.31	4.75	337.0
mm	63.5	106.4	363.6	120.7	
Inches	3	4.63	16.63	5.25	536.0
mm	76.2	117.5	422.2	133.4	
Inches	4	5.50	15.50	5.25	960.0
mm	101.6	139.7	393.7	133.4	
+ Non Shoo	k	Po	, 5		

† Non-Shock Rev 5



MINOVATION IN EVERY VALVE



The information presented on this sheet is correct at the time of publication. Milwaukee Valve reserves the right to change design, and/or material specifications without notice. For the Installation, Operation and Maintenance Manual (IOM) see the engineering section on our website. For the most current information access www.milwaukeevalve.com

www.milwaukeevalve.com