

FR Series



Fire Rated Wall Access Doors

Doors are Fire Rated by Underwriters Laboratories Inc., for 1-1/2 hours, "B" Label, and meet ANSI-UL 10B standard. Door has a heavy duty spring closer to assure positive latching when panel closes. *This door is for wall installation only.*

Door and Frame are fabricated from 16 gage, galvannealed steel with a prime coat finish.

Door has a heavy duty spring to assure positive latching.

Frame is equipped with both masonry anchors and bolt holes to facilitate installation in all types of wall construction.

Concealed Hinge operates completely out of sight so that only the door and frame is visible.

Exterior Latch is recessed and is operated using a ring attached to the sliding bolt.

Interior Latch Release Slide is included enabling door to be opened from the inside.

Finish is a prime coat suitable for painting.

Guide Specification

Provide Elmdor® FR Series, Fire Rated Access Doors (specify model number and options). Access door and frame shall be fabricated from 16 gage, galvannealed steel with a prime coat finish. Hinge shall be concealed type. Door shall have a heavy duty spring to provide positive latching when closed, and an interior latch release slide enabling door to be opened from the inside. Exterior latch shall be recessed and operated using ring attached to the sliding bolt. Finish shall be a prime coat suitable for painting.

FR *Revised: 3/1/02*



MODEL NUMBER AND OPTIONS SELECTION

BASE MODEL NUMBER

☐ FR Fire Rated Access Door

Suffix Options

□ -CL	Cylinder Lock (one per door)
🔲 -GB	Galvanized Drywall Bead
🔲 -SS	Stainless Steel Construction.
	(Type 304 No 4 Finish Satin Finish)


STANDARD AVAILABLE SIZES


Special sizes available upon request.

opecial sizes available apoli request.				
NOMINAL DOOR SIZE (W X H)	WALL OPENING (minimum required)	LATCHES	WEIGHT	
FR 8" x 8"	8-3/8" x 8-3/8"	1	6 lbs.	
FR 10" x 10"	10-3/8" x 10-3/8"	1	7.5 lbs.	
FR 12" x 12"	12-3/8" x 12-3/8"	1	9 lbs.	
FR 12" x 18"	12-3/8" x 18-3/8"	1	10.5 lbs.	
FR 12" x 24"	12-3/8" x 24-3/8"	1	13 lbs.	
FR 14" x 14"	14-3/8" x 14-3/8"	1	10 lbs.	
FR 16" x 16"	16-3/8" x 16-3/8"	1	12.5 lbs.	
FR 18" x 18"	18-3/8" x 18-3/8"	1	15 lbs.	
FR 20" x 20"	20-3/8" x 20-3/8"	1	18 lbs.	
FR 22" x 22"	22-3/8" x 22-3/8"	1	22 lbs.	
FR 22" x 30"	22-3/8" x 30-3/8"	2	28 lbs.	
FR 24" x 24"	24-3/8" x 24-3/8"	2	24.5 lbs.	
FR 24" x 36"	24-3/8"x 36-3/8"	2	33 lbs.	
FR 24" x 48"	24-3/8" x 48-3/8"	2	42 lbs.	
FR 30" x 30"	30-3/8" x 30-3/8"	2	33.5 lbs.	
FR 32" x 32"	32-3/8" x 32-3/8"	2	35 lbs.	
FR 36" x 36"	36-3/8" x 36-3/8"	2	43 lbs.	
FR 36" x 48"	36-3/8" x 48-3/8"	2	74 lbs.	

NOTES:

- 1. CHIP OUT MASONRY TO CLEAR BOLT COVER
- 2. CONCEALED HINGE
- 3. DOOR
- 4. RECESSED LATCH
- 5. INTERIOR LATCH RELEASE SLIDE 6. CLOSING SPRING
- 7. FRAME





Dimensions are subject to manufacturer's tolerance of plus or minus 1/4". Elmdor/Stoneman assumes no responsibility for use of void or suspended data. Please visit www.elmdorstoneman.com for most current specifications. © Copyright 2005 Elmdor/Stoneman, City of Industry, CA, A Division of Acorn Engineering Company.

SELECTION SUMMARY & APPROVAL FOR MANUFACTURING			
Model Number & Options	Quantity		
Company	Date		
Contact	Title		
Approval for Manufacturing/Signature			

FR Revised: 3/1/02