

**NIBCO**

1516 Middlebury Street  
Elkhart, IN 46516-4740

**Phone:** 574.295.3000 • **Fax:** 800.234.0557

**E-Mail:** [info@nibco.com](mailto:info@nibco.com) • **Web site:** [www.nibco.com](http://www.nibco.com)

## Material Number NL99K48, T-595-S6-R-66-LL - Three-Piece Stainless Steel Ball Valve - Full Port, Threaded

The NIBCO® stainless steel ball valve provides ease of operation with quarter-turn (90 degrees) open to close. The reinforced PTFE seat ring and stainless steel ball/stem exhibits high chemical resistance properties and is recommended for process piping. Please refer to NIBCO technical data sheets, valve selection guides, chemical resistance guide and catalog for engineering and installation information. Choose NIBCO® ball valves for the most specified, versatile and economical valve option in

[+ more](#)



### Specifications

<b>UPC Code</b>	039923794086
<b>Type</b>	Ball Valve
<b>Valve Size</b>	3/4
<b>Connection Type</b>	T -- Female NPT Thread (FIPT)
<b>Seal Material</b>	RPTFE (Reinforced)
<b>Seat Material</b>	RPTFE (Reinforced)
<b>Stem Material</b>	SS - Stainless Steel

Ball Material	SS - Stainless Steel
Body Material	Stainless Steel
Cv Coefficient	37
Valve Operator	CS Locking Lever Handle
Description	T595S6R66LL 3/4 THRD BALL 3PC LKG LEV SS
eClass Classification	Stainless Steel Ball Valves
Turns/Operation	Quarter-Turn
Weight	1.91 lb