GATE 105

BRONZE

125 lb. SWP-200 lb. WOG† • General Service Solid Wedge Disc • Non-Rising Stem Threaded Bonnet • Gland Packed • Threaded Ends

4" size has split wedge and bolted bonnet. It is not covered in MSS SP-80.

SPECIFICATIONS

105 Conforms to: MSS SP-80. Type 1, Class 125, Threaded Ends.


MATERIAL LIST

NO.	PART	MATERIAL	SPECIFICATION	
1	Body	Bronze	ASTM B 62	
2	Bonnet	Bronze	ASTM B 62	
3	Wedge	Bronze	ASTM B 62	
4	Stem	Bronze	ASTM B 62	
5	Stuff Nut	Brass	ASTM B283 C37700	
6	Check Nut	Brass	ASTM B283 C37700	
7 1	Gland	Brass	ASTM B124 C37700	
8	Wheel Nut	Brass	Commercial	
9	Handwheel	Mall. Iron	Commercial	
10	Packing	Graphite	Commercial	
11	Name Plate	Sh. Alum.	Commercial	
	•		•	

Not used on 1/2" and smaller.

DIMENDIONO INCLIES / MIL IMETERS							
DIMENSIONS - INCHES / MILIMETERS							
Units	Size	Α	В	С	Cv		
Inches	1/4	1.75	3.63	2.00	5.6		
mm	6.4	44.5	92.1	50.8	5.0		
Inches	3/8	1.81	3.63	2.00	10.7		
mm	9.5	46.1	92.1	50.8	10.7		
Inches	1/2	2.00	3.63	2.00	17.6		
mm	12.7	50.8	92.1	50.8	17.6		
Inches	3/4	2.13	4.38	2.50	32.0		
mm	19.1	54.0	111.1	63.5			
Inches	1	2.56	5.00	2.75	54.0		
mm	25.4	65.1	127.0	69.9			
Inches	1 1/4	2.78	5.31	3.13	97.0		
mm	31.8	70.6	135.0	79.4	97.0		
Inches	1 1/2	2.81	6.34	3.50	135.0		
mm	38.1	71.5	161.1	88.9	135.0		
Inches	2	3.31	7.44	3.75	230.0		
mm	50.8	84.2	188.9	95.3	230.0		
Inches	2 1/2	4.19	9.13	4.75	337.0		
mm	63.5	106.4	231.8	120.7	337.0		
Inches	3	4.63	10.47	5.25	536.0		
mm	76.2	117.5	265.9	133.4	550.0		
Inches	4	5.50	15.50	5.25	960.0		
mm	101.6	139.7	393.7	133.4	900.0		
+ Non Charle							

† Non-Shock Rev 5







www.milwaukeevalve.com

The information presented on this sheet is correct at the time of publication. Milwaukee Valve reserves the right to change design, and/or material specifications without notice. For the Installation, Operation and Maintenance Manual (IOM) see the engineering section on our website. For the most current information access www.milwaukeevalve.com