

## **CHESTERFIELD**

## Bridge Style Lavatory Faucet

1030B









#### Brass valve bodies

**Features** 

- Quarter-turn washerless ceramic disc valve cartridges
- ADA compliant handles

· Solid brass construction

- Swivel spout assembly
- Pop-up knob assembly with drain and tailpiece
- 6-3/8" (16.2 cm) spout height at outlet
- 7-3/16" (18.3 cm) spout reach (c-c)
- For 8" (20.3 cm) centers Maximum 9-3/4" (24.8 cm)
- 1.5 gallons (5.7 liters) per minute maximum flow rate

#### **Codes / Standards Compliance**

Meets or exceeds the following at date of manufacture:

- ASME A112.18.1/CSA B125.1
- IAPMO/<sub>c</sub>UPC
- IPC
- NSF 61
- ADA
- ICC/ANSI A117.1
- Energy Policy Act of 1992
- All applicable US Federal and State material regulations
- $\bullet \ \mathsf{EPA} \ \mathsf{WaterSense}_{\scriptscriptstyle{\textcircled{\tiny{\$}}}}$

#### **Colors / Finishes**

10B: Oil Rubbed Bronze15: Polished Nickel15S: Satin Nickel

• 26: Polished Chrome

• Other: Refer to the Newport Brass catalog for additional color/finish options.

# Specified Model Model Description Colors / Finishes 1030B Bridge Style Lavatory Faucet 10B 15 15S 26 Other

#### **Product Specification:**

#### Add "Color / Finish" suffix to Model number, below.

The two-handle Bridge Style Lavatory Faucet shall be made of solid brass construction. Faucet shall feature brass valve bodies. Faucets shall feature quarter-turn washerless ceramic disc valve cartridges. Faucet shall have a 1.5 gallon (5.7 L) per minute maximum flow rate. Product shall be for 8" centers (20.3 cm) - Maximum 9-3/4" (524.8 cm). Product shall have a 6-3/8" (16.2 cm) spout height at outlet, 7-3/16" (18.3 cm) spout reach (c-c), include a pop-up knob assembly with drain and tailpiece and ADA compliant handles. Faucet shall be Newport Brass Model 1030B/\_\_\_\_\_.

### **Product Dimensions** (units are in inches)

