



Job Name:

Job Type:

Comments:

Quantity:

40076-962: Four-Light Pemberton Wall/Bath

Dimensions:

Width: 29"

Extends: 8"

Height: 10"

Wire: 6 1/2"

Mounting Proc.: Center Lock-Up

Connection: Mounted To Box



Bulbs:

- 4 - medium A - Line 100w Max. 120v - Not included
- 4 - LED Medium LED A-19 8w 120v - Not included
- 4 - LED Medium LED A-19 13.5w 120v - Not included

Features:

- Fixture may be mounted in the up or down position

Material List:

1 Body - Steel - Brushed Nickel

Safety Listing:

UL Listed for Damp Locations
cUL Listed for Damp Locations

Collection: Pemberton

Four Light Bath Bar in Brushed Nickel Finish with Satin Etched Glass Shades.

Sweeping curves in brushed nickel finish and satin etched glass- a soft, contemporary touch.

Design #: D20038

UPC #:785652400797

Finish: Brushed Nickel (962)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Shade	Glass	Satin Etched	1					5				

Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Back Plate					5 1/2	4 1/2

Replacement Bulb Data:

Product #	Type	Base	Watts	Watts Consumed	Volts	Hours	Lumens	Temp (°K)	CRI
97308S	A-19	E-26 Medium			120v	50000	425	3000	85
97309S	A-19	E-26 Medium			120v	50000	850	3000	85

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	UPS Ship
Individual	40076-962	1	785652400797	28	9.25	11.75	1.761	12.2	Yes
NJ Pallet		36		48	40	72	80	440	No

NV Pallet		36		48	40	72	80	440	No
-----------	--	----	--	----	----	----	----	-----	----