



Job Name:

Job Type:

Comments:

Quantity:

65075-962: Three-Light Pemberton Pendant



Dimensions:

Diameter: 18"

Height w/ Chain: 145 3/4"

Height: 24 1/2"

Wire: 144" (color/Clear)

Chain: 120"

Mounting Proc.: Center Lock-Up

Connection: Mounted To Box

Bulbs:

- 3 - medium A - Line 100w Max. 120v - Not included
- 3 - LED Medium LED A-19 8w 120v - Not included
- 3 - LED Medium LED A-19 13.5w 120v - Not included

Features:

- Supplied with 12' of Wire Pre-laced through 10' of Chain

Material List:

- 1 Body - Steel - Brushed Nickel
- 1 Chain - Steel - Brushed Nickel

Safety Listing:

- UL Listed for Dry Locations
- cUL Listed for Dry Locations

Instruction Sheets:

- English (HC-692)
- French (F-004)

Collection: Pemberton

Three Light Pendant in Brushed Nickel Finish with Satin Etched Glass.

Sweeping curves in brushed nickel finish and satin etched glass- a soft, contemporary touch.

Design #: D20008

UPC #:785652650796

Finish: Brushed Nickel (962)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Bowl	Glass	Satin Etched	1					16 3/4				

Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Canopy			1 1/4	5 3/4		

Replacement Bulb Data:

Product #	Type	Base	Watts	Watts Consumed	Volts	Hours	Lumens	Temp (°K)	CRI
97308S	A-19	E-26 Medium			120v	50000	425	3000	85
97309S	A-19	E-26 Medium			120v	50000	850	3000	85

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	UPS Ship
Individual	65075-962	1	785652650796	19.75	19	22.75	4.94	17.622	Yes
NJ Pallet		12		48	40	72	80	211.5	No

NV Pallet		12		48	40	72	80	211.5	No
-----------	--	----	--	----	----	----	----	-------	----